

# PHILIPS

Filament Bulb  
Frosted 60W A19 E26

LED

5000/2700/3000/3500/4000  
K

800lm

15000h

Dimming

046677580186



## A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### Choose a simple replacement for your old bulbs

- Perfect fit and high-quality finishing

# Highlights

## Perfect fit

With a familiar shape, these bulbs are the perfect fit for your existing fixtures. They look just like the classic light bulb.

# Specifications

## Bulb characteristics

- Intended use: Indoor/Outdoor
- Lamp shape: Non directional bulb
- Socket: E26
- Type of glass: Frosted
- Bulb Finish: Frosted
- Dimmable: Only with specific dimmers
- Bulb Material: Glass

## Bulb dimensions

- Height: 11 cm
- Width: 6 cm

## Design and finishing

- Material: Glass

## Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 hour(s)

## Light characteristics

- Color rendering index (CRI): 90
- Color temperature: 5000/2700/3000/3500/4000 K
- Nominal luminous flux: 800 lm
- Warm-up time to 60% light: instant full light
- Color Code: 5000/2700/3000/3500/4000

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

## Other characteristics

- Efficacy: 114 lm/W

## Packaging information

- EAN: 046677580186
- EOC: 580183
- Product title: 7A19/WhiteD/5CCT/FR/G/E26/D 4/1PF T20 CA

## Power consumption

- Power factor: 0.7
- Voltage: 120 V
- Wattage: 7 W
- Wattage equivalent: 60 W

## Product dimensions and weight

- Length: 11 cm

## Technical specifications

- Frequency: 60 Hz

## Packaging dimensions and weight

- EAN/UPC - product: 046677580186
- Net weight: 0.04 kg
- Gross weight: 0.07 kg
- Height: 17.1 cm
- Length: 6.6 cm
- Width: 7.6 cm
- Material number (12NC): 929003126805



Issue date: 2024-05-23  
Version: 0.57

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)