

## Listra Wall Light 11W

Outdoor luminaires

3000K

Black

Water Resistant



046677582913



## Create great outdoor moments

The Philips wall light illuminates and lightens up your entrance with diffused and warm white light.

### Easy installation

- Easy installation

### Sustainable light solutions

- Long lifetime up to 25,000 hours

### Special characteristics

- Powerful light

# Highlights

## Easy installation



Installing a luminaire can be sometimes difficult. With this Philips luminaire, you can be sure that high attention has been given to facilitate it and simplify it

for you. You'll find clear guidance about where you can install the product and relevant information about water-resistant IP ratings.

## Long lifetime up to 25,000 hours



Reliable high-quality LED light lasts up to 25,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while enjoying the perfect garden light every night.

## Powerful light

This Philips outdoor luminaire provides powerful light. A bright pool of light to light up your garden or terrace.

# Specifications

## Design and finishing

- Color: Black
- Material: Metal

## Durability

- Nominal lifetime: 25,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Anti rust anti dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: No
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: No
- Solar Energy: No
- Centerpiece: No

## Garden area

- Garden area: Garden & Patio

## Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 3000 K

## Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Water Resistant

**Product dimensions and weight**

- Net weight: 1.65 kg
- Overall height: 355 mm
- Overall length: 206 mm
- Overall width: 160 mm

**Service**

- Warranty: 2 year(s)

**Packaging dimensions and weight**

- EAN/UPC - product: 046677582913
- Net weight: 1.65 kg
- Gross weight: 1.86 kg
- Height: 41 cm
- Length: 18 cm
- Width: 23 cm

**Technical specifications**

- Total lumen output fixture: 650
- Light color: Neutral white light
- Mains power: 120 V
- Energy class included light source: not applicable
- Class of protection: Class I - Earthed
- Light source replaceable: No
- UL Wet/ damp/ dry location: Wet location



Issue date: 2026-01-11  
Version: 0.108

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)