



Easy control with app or voice

When Edison invented the classic incandescent filament bulb in the 1880s, he could never have imagined what Philips would be able do with them today. These smart LED filament bulbs look great even when they're turned off, but the real magic happens when you turn them on. Fill your rooms with millions of colors and shades of white light from cozy to cool. Enjoy the classic look of vintage incadescent filament bulbs while reaping the energy-saving benefits of LED. And because they have WiZ connected technology on board, you can easily control them using your Wi-Fi and the WiZ app, remote, or your voice.

Easy setup

· Easy plug and play

Smart control

- · Control anywhere with your smartphone.
- · Voice control with Google Assistant, Alexa or Siri Shortcuts

Smart features

- · Automate your light with schedules
- · Preset wellbeing features

Light modes

- Extra warm white light
- Millions of colors and dynamic light modes

Highlights

Easy plug and play



WiZ works with your existing Wi-Fi router, no additional gateway is needed. Simply plug in your new light, download the WiZ app and you're ready to go!

Control from anywhere

Control your WiZ lights wherever you are with smartphone. No need to worry if you've left your lights on before leaving home. WiZ app is available for iOS and Android.

Voice Control

Get hands-free control of your lights by using your voice and Google Assistant, Amazon Alexa or Siri Shortcuts. Use simple voice commands to turn lights on or off, brighten and dim, change color, and set custom light Scenes.

Automate your light with schedules

Automate the lights to fit your daily or weekly routines. Schedule your light to turn on before you arrive home and keep it off when not needed.

Preset wellbeing features

Use the preset wellbeing features in the WiZ app to and enjoy the lighting pattern best suited for your circadian rhythm throughout the day. WiZ will provide you bright daylight when you need to get energized and focus, and transition smoothly to soft warm white to help you relax and sleep better.

Extra warm white light

Create a cozy atmosphere in your home with extra warm white light.

Millions of colors and dynamic light modes



Choose from a palette of millions of light colors to create an amazing atmosphere in your home. Enjoy the subtle differences that our dynamic light effects glow your environment.

Specifications

Bulb characteristics

Intended use: IndoorLamp shape: ST19Socket: E26Type of glass: Clear

Type of glass: CleDimmable: YesBulb Finish: Clear

Bulb dimensions

· Weight: 0.055 kg

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- · Lumen maintenance factor: 70%
- Number of switch cycles: 20,000
- · Nominal lifetime: 15,000

Light characteristics

- · Color consistency: 6 SDCM
- · Color rendering index (CRI): ≥80
- Color temperature: 1800-2100 K
- Light Color Category: Full color
- Nominal luminous flux: 300 lm
- Warm-up time to 60% light: instant
- Luminous Efficacy (rated) (Nom): 47 lm/W

Miscellaneous

EyeComfort: Yes

Other characteristics

· Lamp current: 75 mA

Packaging information

- EAN: 046677584016
- EOC: 584011
- Product title: 6.3ST19/Wi-Fi BLE

Color CL 4/1PF

Power consumption

Power factor: 0.7Voltage: 120 V

Wattage equivalent: 25 WPower Consumption: 6.3 W

Product dimensions and weight

Overall height: 141 mmOverall length: 141 mmOverall width: 64 mm

Rated values

Rated lifetime: 15,000Rated luminous flux: 300 lmRated power: 6.3 W

Technical specifications

• Frequency: 60

What's supported

· Compatible with Effects: Yes

· WiFi: Wireless G

Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999

 Communication protocol: Bluetooth, WiFi (2.4GHz)

Packaging dimensions and weight

• EAN/UPC - product: 046677584016

Net weight: 0.05 kg
Gross weight: 0.11 kg
Height: 16.5 cm
Length: 7.2 cm
Width: 9.9 cm



Issue date: 2025-11-01 Version: 0.150 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips