



Bulb 100W A21 E26

The WiZ LED A21 full color bulb brings smart lighting for your daily living. Retrofit into any lamp shade to create the ambience of your choice. Wi-Fi connected, 16 million colors and adjustable from warm white to daylight.

PRODUCT HIGHLIGHTS

- Full color smart bulb
- Up to 1600 lumens
- Easy plug and play
- Control with app or voice



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!




Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and have lights turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Create your perfect light scene

Make your own mix of different color and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



Millions of colors and changing light modes to make your day

Choose any light color you like or simply apply a dynamic light mode we designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: A21
Socket: E26
Type of glass: Frosted
Dimmable: Yes

BULB DIMENSIONS

Weight: 0.108 kg

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 15,000

LIGHT CHARACTERISTICS

Color consistency: 4 SDCM
Color rendering index (CRI): ≥ 90
Color temperature: 2200-6500 K
Light Color Category: Full color
Nominal luminous flux: 1600 lm
Starting time: < 1 s
Warm-up time to 60% light: instant full light
Luminous Efficacy (rated) (Nom): 110

OTHER CHARACTERISTICS

Lamp current: 165 mA

PACKAGING INFORMATION

EAN: 046677603519
EOC: 603514
Product title: 14.5A21/Wi-Fi BLE
Color/922-65 6/1PF

POWER CONSUMPTION

Power factor: 0.7
Voltage: 120 V
Wattage equivalent: 100 W
Power: 14.5 W

PRODUCT DIMENSIONS AND WEIGHT

Overall height: 138.5 mm
Overall length: 138.5 mm
Overall width: 77 mm

RATED VALUES

Rated lifetime: 15,000
Rated luminous flux: 1600 lm
Rated power: 14.5 W

SERVICE

Warranty: 3 year(s)

TECHNICAL SPECIFICATIONS

Frequency: 60

WHAT'S SUPPORTED

Compatible with Effects: Yes
WiFi: Wireless G
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth
WiFi (2.4GHz)
Compatibility with 3rd party systems:
Alexa Google Home IFTTT
Klikaanklikuit Matter Samsung
Smartthings Sonos

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 046677603519
Net weight: 0.11 kg
Gross weight: 0.15 kg
Height: 18.5 cm
Length: 8.5 cm
Width: 8.5 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.