

Smart Button



This easy-to-use button will surprise you by working everywhere. Stick it on the wall or in a corner without the need for screws or let a metal surface attract the magnet inside. Take it with you around your home and control your lights swiftly.

PRODUCT HIGHLIGHTS

- Battery operated
- IP20/Plastic/white
- Works with all Connected by WiZ products




Battery-powered button to use and leave anywhere

Easily fix the included mounting plate on the wall and the button's integrated magnet will keep it in place. Have fun and try the button directly on other metal surfaces, or simply leave it on a desk or table close to you.



Wireless control of your WiZ lights

Enjoy quick and easy control of your WiZ lights. Turn lights on/off and adjust brightness with just one press. Connects directly to your WiZ lights and works even when the Wi-Fi is down.



Wide control range of 15m / 50ft

Control lights and devices within a range of 15 meters or 50 feet in a normal indoor environment with partitions and walls.



Easily control one or multiple lights in a room

This portable control accessory can link to one room and trigger all lights in that room. Whether there's one or fifty lights! Want to control another room instead? Simply change the accessory's linked room in the app.



Compatible with all "Connected by WIZ" lights

This WiZ control accessory is designed to control all kinds of lights in the WiZ ecosystem. You can use it to control any lights from any brand as long as it's "Connected by WIZ."



The right ambience with just one click

Turn lights on/off with a press, adjust brightness with a long press. The right ambience at your fingertips!



SPECIFICATIONS

DESIGN AND FINISHING

Color: White
Material: Plastic

EXTRA FEATURE/ACCESSORY INCL.

Batteries included: Yes
Control Distance: 15 m

POWER CONSUMPTION

Voltage: 3 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.066 kg
Overall height: 18.5 mm
Overall length: 64 mm
Overall width: 64 mm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Battery type: AAA (LR03)
IP code: IP20 | Finger-protected
Class of protection: Class III - Safe
Extra Low Voltage

WHAT'S SUPPORTED

Compatible with Effects: Yes
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth
WiFi (2.4GHz)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 046677604387
Net weight: 0.07 kg
Gross weight: 0.12 kg
Height: 16.1 cm
Length: 4.6 cm
Width: 7.6 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.