




Filament Globe Clear 25W G25 E26

WiZ filament bulbs are meant to be seen—they look great even when they're turned off. But wait until you turn them on! These dimmable transparent globes of light bathe every corner of your room with all the colors of the rainbow and every shade of white from warm to cool. Enjoy the classic look of vintage incandescent filament bulbs while reaping the energy-saving benefits of LED. All Wi-Fi controllable, of course, using the WiZ app, WiZ remote, or your voice.

PRODUCT HIGHLIGHTS

- Full color smart bulb
- Up to 300 lumens
- Easy plug and play
- Control with app or voice



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and have lights turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.




Millions of colors and changing light modes to make your day

Choose any light color you like or simply apply a dynamic light mode we designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



Control smart lighting the way you like it

WiZ enables you to control smart lighting in multiple ways. Adjust lights with your smartphone, voice, the WiZ remote control, or by using the existing wall switch to toggle between two favorite modes. Works with Google Home, Alexa and Siri Shortcuts.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: G25
Socket: E26
Type of glass: Clear
Dimmable: Yes

BULB DIMENSIONS

Weight: 0.05 kg

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 20,000
Nominal lifetime: 15,000

EXTRA FEATURE/ACCESSORY INCL.

LED integrated: Yes
Solar Energy: No
Warm glow dimmable light: No

LIGHT CHARACTERISTICS

Color consistency: 6 SDCM
Color rendering index (CRI): ≥ 80
Color temperature: 1800-2100 K
Light Color Category: Full color
Nominal luminous flux: 300 lm
Warm-up time to 60% light: instant full light
Luminous Efficacy (rated) (Nom): 47

OTHER CHARACTERISTICS

Lamp current: 75 mA

PACKAGING INFORMATION

EAN: 046677604707
EOC: 604702
Product title: 6.3G25/Wi-Fi BLE Color
CL 6/1PF

POWER CONSUMPTION

Power factor: 0.7
Voltage: 120 V
Wattage equivalent: 25 W
Power: 6.3 W

PRODUCT DIMENSIONS AND WEIGHT

Overall height: 122 mm
Overall length: 122 mm
Overall width: 80 mm

RATED VALUES

Rated lifetime: 15,000
Rated luminous flux: 300 lm
Rated power: 6.3 W

TECHNICAL SPECIFICATIONS

Frequency: 60
Bulb technology: LED

THE BULB

Software upgradable: Yes

WHAT'S SUPPORTED

Compatible with Effects: Yes
WiFi: 802.11b/g/n
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Compatible operating systems: iOS
Android
Communication protocol: Bluetooth
WiFi (2.4GHz)
Compatibility with 3rd party systems:
Alexa Enki Google Home Homey
IFTTT Matter Samsung Smartthings
Siri Shortcuts
Matter functionality: Via 3rd party hubs (Wi-Fi)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 046677604707
Net weight: 0.05 kg
Gross weight: 0.19 kg
Height: 15.5 cm
Length: 10.5 cm
Width: 10.5 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.