



Strip 1 x 9290026960 3000K

1 x 1450 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.00
Service downward 1.00

CIE flux code 46 79 96 100 100

UGRcen (4Hx8H, 0.25H) 25

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80			0.70			0.50			0.30		
	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30
0.60	0.47	0.45	0.44	0.37	0.36	0.32	0.36	0.31	0.29	0.36	0.31	0.29
0.80	0.58	0.55	0.57	0.56	0.54	0.46	0.46	0.41	0.45	0.40	0.38	0.38
1.00	0.67	0.63	0.66	0.64	0.62	0.54	0.53	0.48	0.53	0.48	0.46	0.46
1.25	0.76	0.70	0.74	0.72	0.69	0.62	0.61	0.56	0.60	0.56	0.53	0.53
1.50	0.83	0.75	0.81	0.77	0.74	0.68	0.67	0.62	0.65	0.61	0.59	0.59
2.00	0.93	0.83	0.90	0.86	0.82	0.76	0.75	0.71	0.74	0.70	0.68	0.68
2.50	1.00	0.88	0.97	0.92	0.87	0.82	0.81	0.77	0.79	0.76	0.74	0.74
3.00	1.04	0.91	1.01	0.96	0.90	0.86	0.85	0.81	0.83	0.80	0.78	0.78
4.00	1.10	0.96	1.07	1.00	0.94	0.91	0.89	0.87	0.88	0.86	0.83	0.83
5.00	1.14	0.98	1.11	1.03	0.97	0.94	0.92	0.90	0.91	0.89	0.86	0.86

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	12034	11657	11327	11057	10860	10739	10699
50.0	11947	11504	11119	10809	10583	10446	10401
55.0	11746	11227	10784	10430	10175	10020	9969
60.0	11511	10901	10387	9984	9695	9523	9466
65.0	11035	10319	9732	9278	8958	8768	8706
70.0	10388	9540	8867	8360	8009	7804	7736
75.0	9267	8269	7516	6971	6604	6392	6324
80.0	7735	6537	5713	5156	4797	4596	4532
85.0	5395	3941	3150	2688	2415	2271	2226
90.0	228750	1406	730	517	422	379	366

(cd/m²)

2021-08-11