




DN200 G3 LED12 1 x 9290032717 4000K

1 x 1200 lm

Polar intensity diagram**Quantity estimation diagram****UGR diagram**

Light output ratio 1.00
Service upward 0.00
Service downward 1.00

CIE flux code 46 77 94 100 100

UGRcen (4Hx8H, 0.25H) 28

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.48	0.45	0.47	0.46	0.45	0.37	0.37	0.32	0.36	0.32	0.30	0.30
0.80	0.58	0.55	0.57	0.56	0.54	0.46	0.46	0.41	0.45	0.40	0.38	0.38
1.00	0.67	0.62	0.66	0.63	0.61	0.54	0.53	0.48	0.52	0.48	0.45	0.45
1.25	0.76	0.69	0.74	0.71	0.68	0.61	0.60	0.55	0.59	0.55	0.53	0.53
1.50	0.82	0.74	0.80	0.77	0.73	0.67	0.66	0.61	0.65	0.60	0.58	0.58
2.00	0.92	0.82	0.90	0.85	0.81	0.75	0.74	0.70	0.73	0.69	0.67	0.67
2.50	0.99	0.87	0.96	0.91	0.86	0.81	0.80	0.76	0.78	0.75	0.72	0.72
3.00	1.03	0.91	1.00	0.95	0.89	0.85	0.83	0.80	0.82	0.79	0.76	0.76
4.00	1.09	0.95	1.06	0.99	0.94	0.90	0.88	0.86	0.87	0.84	0.82	0.82
5.00	1.13	0.97	1.10	1.02	0.96	0.93	0.91	0.89	0.90	0.88	0.85	0.85

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	24672	24672	24672	24672	24672	24672	24672
50.0	24270	24270	24270	24270	24270	24270	24270
55.0	23846	23846	23846	23846	23846	23846	23846
60.0	23393	23393	23393	23393	23393	23393	23393
65.0	22942	22942	22942	22942	22942	22942	22942
70.0	22430	22430	22430	22430	22430	22430	22430
75.0	21870	21870	21870	21870	21870	21870	21870
80.0	21214	21214	21214	21214	21214	21214	21214
85.0	20049	20049	20049	20049	20049	20049	20049
90.0	47476	47476	47476	47476	47476	47476	47476

(cd/m²)

2023-01-05