


DN200 G3 LED3 1 x 9290032695 3000K


1 x 280 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00


CIE flux code 50 80 95 100 100

UGRcen (4Hx8H, 0.25H) 28

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80			0.70			0.50			0.30		
	0.80			0.70			0.50			0.30		
	0.50			0.50			0.30			0.10		
0.60	0.50	0.48	0.49	0.48	0.47	0.40	0.40	0.35	0.39	0.35	0.33	0.33
0.80	0.61	0.57	0.60	0.58	0.56	0.49	0.48	0.43	0.48	0.43	0.41	0.41
1.00	0.69	0.64	0.68	0.66	0.64	0.57	0.56	0.51	0.55	0.51	0.48	0.48
1.25	0.78	0.71	0.76	0.73	0.70	0.64	0.63	0.58	0.62	0.58	0.55	0.55
1.50	0.84	0.76	0.82	0.79	0.75	0.69	0.68	0.64	0.67	0.63	0.61	0.61
2.00	0.94	0.84	0.91	0.87	0.83	0.78	0.76	0.72	0.75	0.72	0.69	0.69
2.50	1.00	0.89	0.98	0.92	0.88	0.83	0.81	0.78	0.80	0.77	0.75	0.75
3.00	1.05	0.92	1.02	0.96	0.91	0.87	0.85	0.82	0.84	0.81	0.79	0.79
4.00	1.11	0.96	1.07	1.01	0.95	0.91	0.90	0.87	0.88	0.86	0.83	0.83
5.00	1.14	0.98	1.11	1.03	0.97	0.94	0.92	0.90	0.91	0.89	0.86	0.86

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	26383	26383	26383	26383	26383	26383	26383
50.0	25298	25298	25298	25298	25298	25298	25298
55.0	24213	24213	24213	24213	24213	24213	24213
60.0	23122	23122	23122	23122	23122	23122	23122
65.0	21981	21981	21981	21981	21981	21981	21981
70.0	20775	20775	20775	20775	20775	20775	20775
75.0	19430	19430	19430	19430	19430	19430	19430
80.0	17666	17666	17666	17666	17666	17666	17666
85.0	14580	14580	14580	14580	14580	14580	14580
90.0	14407	14407	14407	14407	14407	14407	14407

(cd/m²)

2023-01-05