


DN200 G3 LED6 1 x 9290032707 3000K


1 x 550 lm

Polar intensity diagram

Light output ratio 1.00
Service upward 0.00
Service downward 1.00


CIE flux code 49 79 95 100 100

UGRcen (4Hx8H, 0.25H) 26

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80 0.80				0.70 0.70 0.70 0.70				0.50 0.50 0.30 0.30			
	0.80	0.50	0.30	0.10	0.80	0.50	0.30	0.10	0.80	0.50	0.30	0.10
0.60	0.50	0.47	0.49	0.48	0.47	0.39	0.39	0.34	0.38	0.34	0.32	
0.80	0.60	0.56	0.59	0.57	0.56	0.48	0.48	0.43	0.47	0.42	0.40	
1.00	0.69	0.64	0.67	0.65	0.63	0.56	0.55	0.50	0.54	0.50	0.48	
1.25	0.77	0.71	0.76	0.73	0.70	0.63	0.62	0.57	0.61	0.57	0.55	
1.50	0.84	0.76	0.82	0.78	0.75	0.69	0.68	0.63	0.66	0.62	0.60	
2.00	0.93	0.83	0.91	0.87	0.82	0.77	0.76	0.72	0.74	0.71	0.69	
2.50	1.00	0.88	0.97	0.92	0.87	0.82	0.81	0.78	0.80	0.77	0.74	
3.00	1.05	0.92	1.02	0.96	0.90	0.86	0.85	0.82	0.83	0.81	0.78	
4.00	1.11	0.96	1.07	1.00	0.95	0.91	0.89	0.87	0.88	0.86	0.83	
5.00	1.14	0.98	1.11	1.03	0.97	0.94	0.92	0.90	0.91	0.89	0.86	

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	16857	16857	16857	16857	16857	16857	16857
50.0	16263	16263	16263	16263	16263	16263	16263
55.0	15651	15651	15651	15651	15651	15651	15651
60.0	15007	15007	15007	15007	15007	15007	15007
65.0	14325	14325	14325	14325	14325	14325	14325
70.0	13582	13582	13582	13582	13582	13582	13582
75.0	12748	12748	12748	12748	12748	12748	12748
80.0	11761	11761	11761	11761	11761	11761	11761
85.0	10257	10257	10257	10257	10257	10257	10257
90.0	13223	13223	13223	13223	13223	13223	13223

(cd/m²)

2023-01-05