


DN200 G3 LED6 1 x 9290032704 3000K


1 x 550 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00


CIE flux code 49 80 95 100 100

UGRcen (4Hx8H, 0.25H) 28

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80				0.70				0.50			
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.49	0.47	0.49	0.47	0.46	0.39	0.39	0.34	0.38	0.34	0.32	0.32
0.80	0.60	0.56	0.59	0.57	0.56	0.48	0.48	0.43	0.47	0.42	0.40	0.40
1.00	0.69	0.64	0.68	0.65	0.63	0.56	0.55	0.50	0.54	0.50	0.48	0.48
1.25	0.77	0.71	0.76	0.73	0.70	0.63	0.62	0.58	0.61	0.57	0.55	0.55
1.50	0.84	0.76	0.82	0.78	0.75	0.69	0.68	0.63	0.67	0.63	0.60	0.60
2.00	0.94	0.84	0.91	0.87	0.83	0.77	0.76	0.72	0.75	0.71	0.69	0.69
2.50	1.00	0.88	0.97	0.92	0.87	0.83	0.81	0.78	0.80	0.77	0.74	0.74
3.00	1.05	0.92	1.02	0.96	0.91	0.86	0.85	0.82	0.83	0.81	0.78	0.78
4.00	1.11	0.96	1.07	1.00	0.95	0.91	0.89	0.87	0.88	0.86	0.83	0.83
5.00	1.14	0.98	1.11	1.03	0.97	0.94	0.92	0.90	0.91	0.89	0.86	0.86

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	27342	27342	27342	27342	27342	27342	27342
50.0	26293	26293	26293	26293	26293	26293	26293
55.0	25223	25223	25223	25223	25223	25223	25223
60.0	24133	24133	24133	24133	24133	24133	24133
65.0	22994	22994	22994	22994	22994	22994	22994
70.0	21793	21793	21793	21793	21793	21793	21793
75.0	20447	20447	20447	20447	20447	20447	20447
80.0	18816	18816	18816	18816	18816	18816	18816
85.0	16196	16196	16196	16196	16196	16196	16196
90.0	9480	9480	9480	9480	9480	9480	9480

(cd/m²)

2023-01-05