


DN200 G3 LED6 1 x 9290032702 4000K


1 x 600 lm

Polar intensity diagram

Light output ratio 1.00
Service upward 0.00
Service downward 1.00


CIE flux code 50 80 96 100 100

UGRcen (4Hx8H, 0.25H) 29

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.50	0.48	0.49	0.48	0.47	0.40	0.40	0.35	0.39	0.35	0.33	0.33
0.80	0.61	0.57	0.60	0.58	0.56	0.49	0.48	0.44	0.48	0.43	0.41	0.41
1.00	0.70	0.65	0.68	0.66	0.64	0.57	0.56	0.51	0.55	0.51	0.48	0.48
1.25	0.78	0.71	0.76	0.73	0.71	0.64	0.63	0.58	0.62	0.58	0.56	0.56
1.50	0.84	0.77	0.82	0.79	0.76	0.69	0.68	0.64	0.67	0.63	0.61	0.61
2.00	0.94	0.84	0.92	0.87	0.83	0.78	0.77	0.73	0.75	0.72	0.69	0.69
2.50	1.01	0.89	0.98	0.93	0.88	0.83	0.82	0.78	0.80	0.78	0.75	0.75
3.00	1.05	0.92	1.02	0.96	0.91	0.87	0.86	0.83	0.84	0.82	0.79	0.79
4.00	1.11	0.96	1.08	1.01	0.95	0.92	0.90	0.88	0.89	0.87	0.84	0.84
5.00	1.15	0.99	1.11	1.04	0.98	0.95	0.93	0.91	0.91	0.90	0.87	0.87

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	37711	37711	37711	37711	37711	37711	37711
50.0	36199	36199	36199	36199	36199	36199	36199
55.0	34661	34661	34661	34661	34661	34661	34661
60.0	33067	33067	33067	33067	33067	33067	33067
65.0	31426	31426	31426	31426	31426	31426	31426
70.0	29634	29634	29634	29634	29634	29634	29634
75.0	27619	27619	27619	27619	27619	27619	27619
80.0	25093	25093	25093	25093	25093	25093	25093
85.0	20961	20961	20961	20961	20961	20961	20961
90.0	12649	12649	12649	12649	12649	12649	12649

(cd/m²)

2023-01-05