


DN200 G3 LED6 1 x 9290032709 6500K


1 x 600 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00


CIE flux code 49 79 95 100 100

UGRcen (4Hx8H, 0.25H) 27

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80 0.80				0.70 0.70				0.50 0.50			
	0.80	0.50	0.30	0.10	0.70	0.50	0.30	0.10	0.50	0.30	0.10	0.00
0.60	0.50	0.47	0.49	0.48	0.47	0.39	0.39	0.34	0.38	0.34	0.32	0.32
0.80	0.60	0.56	0.59	0.57	0.56	0.48	0.48	0.43	0.47	0.42	0.40	0.40
1.00	0.69	0.64	0.67	0.65	0.63	0.56	0.55	0.50	0.54	0.50	0.48	0.48
1.25	0.77	0.71	0.76	0.73	0.70	0.63	0.62	0.57	0.61	0.57	0.55	0.55
1.50	0.84	0.76	0.82	0.78	0.75	0.69	0.68	0.63	0.66	0.62	0.60	0.60
2.00	0.93	0.83	0.91	0.87	0.82	0.77	0.76	0.72	0.74	0.71	0.69	0.69
2.50	1.00	0.88	0.97	0.92	0.87	0.82	0.81	0.78	0.80	0.77	0.74	0.74
3.00	1.05	0.92	1.02	0.96	0.90	0.86	0.85	0.82	0.83	0.81	0.78	0.78
4.00	1.11	0.96	1.07	1.00	0.95	0.91	0.89	0.87	0.88	0.86	0.83	0.83
5.00	1.14	0.98	1.11	1.03	0.97	0.94	0.92	0.90	0.91	0.89	0.86	0.86

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	18357	18357	18357	18357	18357	18357	18357
50.0	17746	17746	17746	17746	17746	17746	17746
55.0	17093	17093	17093	17093	17093	17093	17093
60.0	16442	16442	16442	16442	16442	16442	16442
65.0	15751	15751	15751	15751	15751	15751	15751
70.0	14996	14996	14996	14996	14996	14996	14996
75.0	14114	14114	14114	14114	14114	14114	14114
80.0	13099	13099	13099	13099	13099	13099	13099
85.0	11518	11518	11518	11518	11518	11518	11518
90.0	21261	21261	21261	21261	21261	21261	21261

(cd/m²)

2023-01-05