


DN200 G3 LED6 1 x 9290032703 6500K


1 x 600 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00


CIE flux code 49 80 96 100 100

UGRcen (4Hx8H, 0.25H) 29

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.49	0.47	0.49	0.48	0.46	0.39	0.39	0.34	0.38	0.34	0.32	0.32
0.80	0.60	0.57	0.59	0.57	0.56	0.48	0.48	0.43	0.47	0.43	0.40	0.40
1.00	0.69	0.64	0.68	0.65	0.63	0.56	0.55	0.50	0.54	0.50	0.48	0.48
1.25	0.78	0.71	0.76	0.73	0.70	0.63	0.62	0.58	0.62	0.57	0.55	0.55
1.50	0.84	0.76	0.82	0.79	0.75	0.69	0.68	0.63	0.67	0.63	0.61	0.61
2.00	0.94	0.84	0.91	0.87	0.83	0.78	0.76	0.72	0.75	0.72	0.69	0.69
2.50	1.00	0.89	0.98	0.92	0.88	0.83	0.82	0.78	0.80	0.77	0.75	0.75
3.00	1.05	0.92	1.02	0.96	0.91	0.87	0.85	0.82	0.84	0.81	0.79	0.79
4.00	1.11	0.96	1.08	1.01	0.95	0.92	0.90	0.88	0.88	0.86	0.84	0.84
5.00	1.15	0.99	1.11	1.04	0.97	0.95	0.93	0.91	0.91	0.89	0.87	0.87

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	37800	37800	37800	37800	37800	37800	37800
50.0	36369	36369	36369	36369	36369	36369	36369
55.0	34896	34896	34896	34896	34896	34896	34896
60.0	33343	33343	33343	33343	33343	33343	33343
65.0	31708	31708	31708	31708	31708	31708	31708
70.0	29910	29910	29910	29910	29910	29910	29910
75.0	27821	27821	27821	27821	27821	27821	27821
80.0	25189	25189	25189	25189	25189	25189	25189
85.0	20809	20809	20809	20809	20809	20809	20809
90.0	9481	9481	9481	9481	9481	9481	9481

(cd/m²)

2023-01-05