


DN200 G3 LED6 1 x 9290032706 6500K


1 x 600 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00


CIE flux code 49 80 95 100 100

UGRcen (4Hx8H, 0.25H) 28

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80			0.70			0.50			0.30		
	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30
0.60	0.49	0.47	0.46	0.49	0.47	0.46	0.39	0.39	0.34	0.38	0.34	0.32
0.80	0.60	0.56	0.55	0.59	0.57	0.56	0.48	0.48	0.43	0.47	0.42	0.40
1.00	0.69	0.64	0.63	0.68	0.65	0.63	0.56	0.55	0.50	0.54	0.50	0.48
1.25	0.77	0.71	0.70	0.76	0.73	0.70	0.63	0.62	0.58	0.61	0.57	0.55
1.50	0.84	0.76	0.75	0.82	0.78	0.75	0.69	0.68	0.63	0.67	0.63	0.60
2.00	0.94	0.84	0.83	0.91	0.87	0.83	0.77	0.76	0.72	0.75	0.71	0.69
2.50	1.00	0.88	0.87	0.97	0.92	0.87	0.83	0.81	0.78	0.80	0.77	0.74
3.00	1.05	0.92	0.91	1.02	0.96	0.91	0.86	0.85	0.82	0.83	0.81	0.78
4.00	1.11	0.96	0.95	1.07	1.00	0.95	0.91	0.89	0.87	0.88	0.86	0.83
5.00	1.14	0.98	0.97	1.11	1.03	0.97	0.94	0.92	0.90	0.91	0.89	0.86

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	29905	29905	29905	29905	29905	29905	29905
50.0	28796	28796	28796	28796	28796	28796	28796
55.0	27664	27664	27664	27664	27664	27664	27664
60.0	26494	26494	26494	26494	26494	26494	26494
65.0	25241	25241	25241	25241	25241	25241	25241
70.0	23877	23877	23877	23877	23877	23877	23877
75.0	22346	22346	22346	22346	22346	22346	22346
80.0	20422	20422	20422	20422	20422	20422	20422
85.0	17302	17302	17302	17302	17302	17302	17302
90.0	10357	10357	10357	10357	10357	10357	10357

(cd/m²)

2023-01-05