



1 x 9290023221 18W 6500K

1 x 1300 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.01
Service downward 0.99

CIE flux code 47 78 95 99 100

UGRcen (4Hx8H, 0.25H) 26

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80			0.70			0.50			0.30		
	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30
0.60	0.48	0.46	0.47	0.46	0.45	0.38	0.37	0.32	0.37	0.32	0.30	0.30
0.80	0.59	0.55	0.58	0.56	0.54	0.47	0.46	0.41	0.45	0.41	0.39	0.39
1.00	0.68	0.63	0.66	0.64	0.62	0.54	0.54	0.48	0.53	0.48	0.46	0.46
1.25	0.76	0.70	0.74	0.71	0.69	0.62	0.61	0.56	0.60	0.55	0.53	0.53
1.50	0.83	0.75	0.81	0.77	0.74	0.67	0.66	0.62	0.65	0.61	0.58	0.58
2.00	0.93	0.83	0.90	0.86	0.81	0.76	0.75	0.70	0.73	0.70	0.67	0.67
2.50	0.99	0.88	0.96	0.91	0.86	0.82	0.80	0.76	0.78	0.75	0.73	0.73
3.00	1.04	0.91	1.01	0.95	0.90	0.86	0.84	0.81	0.82	0.79	0.77	0.77
4.00	1.10	0.95	1.06	1.00	0.94	0.90	0.89	0.86	0.87	0.85	0.82	0.82
5.00	1.14	0.98	1.10	1.03	0.96	0.94	0.92	0.89	0.90	0.88	0.85	0.85

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	13658	13640	13629	13626	13629	13640	13658
50.0	13392	13372	13359	13355	13359	13372	13392
55.0	13072	13048	13033	13028	13033	13048	13072
60.0	12704	12676	12659	12653	12659	12676	12704
65.0	12273	12240	12219	12212	12219	12240	12273
70.0	11751	11711	11685	11677	11685	11711	11751
75.0	11085	11034	11001	10990	11001	11034	11085
80.0	10172	10101	10057	10042	10057	10101	10172
85.0	8222	8111	8042	8019	8042	8111	8222
90.0	2000	1633	1464	1414	1464	1633	2000

(cd/m²)

2019-11-08