



1 x 929002345600 6W 6500K

1 x 400 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.01
Service downward 0.99

CIE flux code 48 79 96 99 100

UGRcen (4Hx8H, 0.25H) 27

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80			0.70			0.50			0.30		
	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30
0.60	0.49	0.46	0.48	0.47	0.46	0.39	0.38	0.33	0.37	0.33	0.31	0.31
0.80	0.59	0.56	0.58	0.57	0.55	0.48	0.47	0.42	0.46	0.42	0.39	0.39
1.00	0.68	0.63	0.67	0.65	0.62	0.55	0.54	0.49	0.53	0.49	0.47	0.47
1.25	0.77	0.70	0.75	0.72	0.69	0.63	0.61	0.57	0.60	0.56	0.54	0.54
1.50	0.83	0.76	0.81	0.78	0.75	0.68	0.67	0.62	0.66	0.62	0.59	0.59
2.00	0.93	0.83	0.91	0.86	0.82	0.77	0.75	0.71	0.74	0.70	0.68	0.68
2.50	1.00	0.88	0.97	0.92	0.87	0.82	0.81	0.77	0.79	0.76	0.74	0.74
3.00	1.05	0.92	1.01	0.96	0.90	0.86	0.85	0.82	0.83	0.80	0.78	0.78
4.00	1.11	0.96	1.07	1.00	0.94	0.91	0.89	0.87	0.88	0.85	0.83	0.83
5.00	1.14	0.98	1.11	1.03	0.97	0.94	0.92	0.90	0.90	0.89	0.86	0.86

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	22883	22815	22773	22759	22773	22815	22883
50.0	22319	22241	22192	22175	22192	22241	22319
55.0	21659	21568	21512	21492	21512	21568	21659
60.0	20887	20781	20715	20693	20715	20781	20887
65.0	19982	19858	19781	19755	19781	19858	19982
70.0	18863	18715	18623	18591	18623	18715	18863
75.0	17411	17228	17115	17076	17115	17228	17411
80.0	15181	14945	14800	14752	14800	14945	15181
85.0	10408	10107	9927	9867	9927	10107	10408
90.0	1867	1524	1366	1320	1366	1524	1867

(cd/m²)

2019-11-11