



1 x 929002346300 24W 3000K

1 x 2000 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.01
Service downward 0.99

CIE flux code 46 77 95 99 100

UGRcen (4Hx8H, 0.25H) 25

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80			0.70			0.50			0.30		
	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30
0.60	0.48	0.50	0.52	0.47	0.49	0.51	0.46	0.48	0.50	0.45	0.47	0.49
0.80	0.58	0.55	0.57	0.57	0.55	0.54	0.46	0.40	0.45	0.40	0.38	0.36
1.00	0.67	0.62	0.65	0.63	0.61	0.54	0.53	0.48	0.52	0.47	0.45	0.43
1.25	0.75	0.69	0.74	0.71	0.68	0.61	0.60	0.55	0.59	0.55	0.52	0.50
1.50	0.82	0.74	0.80	0.77	0.73	0.67	0.66	0.61	0.64	0.60	0.58	0.56
2.00	0.92	0.82	0.90	0.85	0.81	0.75	0.74	0.70	0.73	0.69	0.66	0.64
2.50	0.99	0.87	0.96	0.91	0.86	0.81	0.80	0.76	0.78	0.75	0.72	0.70
3.00	1.04	0.91	1.00	0.95	0.89	0.85	0.83	0.80	0.82	0.79	0.76	0.74
4.00	1.10	0.95	1.06	1.00	0.94	0.90	0.88	0.86	0.87	0.84	0.81	0.79
5.00	1.14	0.98	1.10	1.03	0.96	0.93	0.91	0.89	0.90	0.88	0.85	0.83

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	9820	9811	9806	9804	9806	9811	9820
50.0	9652	9642	9636	9634	9636	9642	9652
55.0	9463	9451	9444	9441	9444	9451	9463
60.0	9251	9237	9228	9225	9228	9237	9251
65.0	9005	8988	8977	8974	8977	8988	9005
70.0	8729	8708	8695	8690	8695	8708	8729
75.0	8418	8391	8374	8368	8374	8391	8418
80.0	8074	8035	8011	8002	8011	8035	8074
85.0	7662	7589	7544	7528	7544	7589	7662
90.0	14039	11463	10277	9927	10277	11463	14039

(cd/m²)

2019-11-11