



1 x 929002346500 24W 6500K

1 x 2000 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.01
Service downward 0.99

CIE flux code 46 78 95 99 100

UGRcen (4Hx8H, 0.25H) 25

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80			0.70			0.50			0.30		
	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30
0.60	0.47	0.45	0.44	0.46	0.45	0.44	0.37	0.36	0.32	0.36	0.31	0.29
0.80	0.58	0.55	0.54	0.57	0.55	0.54	0.46	0.45	0.40	0.45	0.40	0.38
1.00	0.67	0.62	0.61	0.66	0.63	0.61	0.54	0.53	0.48	0.52	0.47	0.45
1.25	0.76	0.69	0.68	0.74	0.71	0.68	0.61	0.60	0.55	0.59	0.55	0.52
1.50	0.82	0.75	0.74	0.80	0.77	0.74	0.67	0.66	0.61	0.65	0.60	0.58
2.00	0.92	0.82	0.81	0.90	0.85	0.81	0.76	0.74	0.70	0.73	0.69	0.67
2.50	0.99	0.87	0.86	0.96	0.91	0.86	0.81	0.80	0.76	0.78	0.75	0.72
3.00	1.04	0.91	0.90	1.01	0.95	0.90	0.85	0.84	0.80	0.82	0.79	0.76
4.00	1.10	0.95	0.94	1.06	1.00	0.94	0.90	0.88	0.86	0.87	0.84	0.81
5.00	1.14	0.97	0.96	1.10	1.03	0.96	0.93	0.91	0.89	0.89	0.88	0.85

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	9845	9837	9831	9829	9831	9837	9845
50.0	9669	9659	9653	9651	9653	9659	9669
55.0	9471	9460	9452	9450	9452	9460	9471
60.0	9242	9228	9219	9216	9219	9228	9242
65.0	8989	8972	8962	8958	8962	8972	8989
70.0	8689	8668	8655	8651	8655	8668	8689
75.0	8351	8324	8308	8302	8308	8324	8351
80.0	7943	7904	7880	7872	7880	7904	7943
85.0	7287	7218	7175	7160	7175	7218	7287
90.0	3804	3106	2785	2690	2785	3106	3804

(cd/m²)

2019-11-11