



1 x 929002345800 6W 4000K

1 x 400 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.01
Service downward 0.99

CIE flux code 49 80 96 99 100

UGRcen (4Hx8H, 0.25H) 27

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80 0.80			0.70 0.70 0.70			0.50 0.50			0.30 0.30		
	0.50 0.50			0.50 0.50 0.30			0.30 0.10			0.30 0.10		
	0.30 0.10			0.30 0.20 0.10			0.10 0.10			0.10 0.10		
0.60	0.49	0.47	0.48	0.47	0.46	0.39	0.39	0.34	0.38	0.34	0.32	
0.80	0.60	0.56	0.59	0.57	0.56	0.48	0.48	0.43	0.47	0.42	0.40	
1.00	0.69	0.64	0.67	0.65	0.63	0.56	0.55	0.50	0.54	0.50	0.47	
1.25	0.77	0.71	0.76	0.73	0.70	0.63	0.62	0.57	0.61	0.57	0.54	
1.50	0.84	0.76	0.82	0.78	0.75	0.69	0.68	0.63	0.66	0.62	0.60	
2.00	0.94	0.84	0.91	0.87	0.83	0.77	0.76	0.72	0.74	0.71	0.68	
2.50	1.00	0.89	0.97	0.92	0.87	0.83	0.81	0.78	0.80	0.77	0.74	
3.00	1.05	0.92	1.02	0.96	0.91	0.87	0.85	0.82	0.83	0.81	0.78	
4.00	1.11	0.96	1.07	1.01	0.95	0.91	0.90	0.87	0.88	0.86	0.83	
5.00	1.15	0.98	1.11	1.03	0.97	0.94	0.92	0.90	0.91	0.89	0.86	

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	23047	22979	22936	22922	22936	22979	23047
50.0	22351	22273	22224	22208	22224	22273	22351
55.0	21555	21465	21409	21390	21409	21465	21555
60.0	20633	20529	20464	20442	20464	20529	20633
65.0	19516	19395	19319	19294	19319	19395	19516
70.0	18131	17988	17900	17870	17900	17988	18131
75.0	16299	16127	16021	15985	16021	16127	16299
80.0	13373	13165	13037	12995	13037	13165	13373
85.0	6956	6755	6635	6595	6635	6755	6956
90.0	2133	1742	1562	1508	1562	1742	2133

(cd/m²)