


DN020 G3 LED3 CW 3.5W 220-240V 1 x 9290025084 6500K


1 x 300 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00


CIE flux code 47 78 95 100 100

UGRcen (4Hx8H, 0.25H) 29

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)												
	0.80 0.80			0.70 0.70 0.70 0.70				0.50 0.50		0.30 0.30			0.00
	0.50 0.50			0.50 0.50 0.50 0.30				0.30 0.10		0.10 0.10			0.00
	0.30 0.10			0.30 0.20 0.10 0.10				0.10 0.10					0.00
0.60	0.48	0.46	0.47	0.46	0.45	0.38	0.37	0.33	0.37	0.33	0.31		
0.80	0.59	0.55	0.58	0.56	0.55	0.47	0.46	0.41	0.46	0.41	0.39		
1.00	0.68	0.63	0.66	0.64	0.62	0.55	0.54	0.49	0.53	0.48	0.46		
1.25	0.76	0.70	0.75	0.72	0.69	0.62	0.61	0.56	0.60	0.56	0.53		
1.50	0.83	0.75	0.81	0.77	0.74	0.68	0.67	0.62	0.65	0.61	0.59		
2.00	0.93	0.83	0.90	0.86	0.82	0.76	0.75	0.71	0.74	0.70	0.68		
2.50	0.99	0.88	0.97	0.91	0.87	0.82	0.80	0.77	0.79	0.76	0.73		
3.00	1.04	0.91	1.01	0.95	0.90	0.86	0.84	0.81	0.83	0.80	0.77		
4.00	1.10	0.95	1.07	1.00	0.94	0.91	0.89	0.86	0.87	0.85	0.83		
5.00	1.14	0.98	1.10	1.03	0.97	0.94	0.92	0.90	0.90	0.88	0.86		

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	31947	31947	31947	31947	31947	31947	31947
50.0	31227	31227	31227	31227	31227	31227	31227
55.0	30390	30390	30390	30390	30390	30390	30390
60.0	29414	29414	29414	29414	29414	29414	29414
65.0	28124	28124	28124	28124	28124	28124	28124
70.0	26587	26587	26587	26587	26587	26587	26587
75.0	24390	24390	24390	24390	24390	24390	24390
80.0	21105	21105	21105	21105	21105	21105	21105
85.0	14709	14709	14709	14709	14709	14709	14709
90.0	6895	6895	6895	6895	6895	6895	6895

(cd/m²)

2020-08-24