


Downlight 1 x 9290026756 6500K


1 x 1300 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00


CIE flux code 48 80 96 100 100

UGRcen (4Hx8H, 0.25H) 26

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80 0.80				0.70 0.70				0.50 0.50			
	0.80	0.50	0.30	0.10	0.70	0.50	0.30	0.10	0.50	0.30	0.10	0.00
0.60	0.49	0.46	0.48	0.47	0.46	0.38	0.38	0.33	0.37	0.33	0.31	0.31
0.80	0.60	0.56	0.58	0.57	0.55	0.48	0.47	0.42	0.46	0.42	0.40	0.40
1.00	0.69	0.64	0.67	0.65	0.63	0.56	0.55	0.50	0.54	0.49	0.47	0.47
1.25	0.77	0.71	0.75	0.73	0.70	0.63	0.62	0.57	0.61	0.57	0.54	0.54
1.50	0.84	0.76	0.82	0.78	0.75	0.69	0.68	0.63	0.66	0.62	0.60	0.60
2.00	0.94	0.84	0.91	0.87	0.83	0.77	0.76	0.72	0.75	0.71	0.69	0.69
2.50	1.00	0.89	0.97	0.92	0.87	0.83	0.81	0.78	0.80	0.77	0.74	0.74
3.00	1.05	0.92	1.02	0.96	0.91	0.87	0.85	0.82	0.84	0.81	0.79	0.79
4.00	1.11	0.96	1.07	1.01	0.95	0.92	0.90	0.87	0.88	0.86	0.83	0.83
5.00	1.15	0.98	1.11	1.04	0.97	0.94	0.93	0.91	0.91	0.89	0.86	0.86

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	18798	18798	18798	18798	18798	18798	18798
50.0	18325	18325	18325	18325	18325	18325	18325
55.0	17757	17757	17757	17757	17757	17757	17757
60.0	17069	17069	17069	17069	17069	17069	17069
65.0	16193	16193	16193	16193	16193	16193	16193
70.0	15044	15044	15044	15044	15044	15044	15044
75.0	13522	13522	13522	13522	13522	13522	13522
80.0	11499	11499	11499	11499	11499	11499	11499
85.0	8389	8389	8389	8389	8389	8389	8389
90.0	9137	9137	9137	9137	9137	9137	9137

(cd/m²)

2022-04-23