


Downlight 1 x 9290026754 3000K


1 x 1200 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00


CIE flux code 47 79 96 100 100

UGRcen (4Hx8H, 0.25H) 26

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.80	0.80	0.70	0.70	0.70
0.60	0.48	0.46	0.47	0.46	0.45	0.38	0.37	0.32	0.37	0.32	0.30	0.48	0.46	0.47	0.46	0.45
0.80	0.59	0.55	0.58	0.56	0.55	0.47	0.46	0.41	0.46	0.41	0.39	0.59	0.55	0.58	0.56	0.55
1.00	0.68	0.63	0.66	0.64	0.62	0.55	0.54	0.49	0.53	0.49	0.46	0.68	0.63	0.66	0.64	0.62
1.25	0.77	0.70	0.75	0.72	0.69	0.62	0.61	0.56	0.60	0.56	0.54	0.77	0.70	0.75	0.72	0.69
1.50	0.83	0.75	0.81	0.78	0.74	0.68	0.67	0.62	0.66	0.62	0.59	0.83	0.75	0.81	0.78	0.74
2.00	0.93	0.83	0.91	0.86	0.82	0.77	0.75	0.71	0.74	0.71	0.68	0.93	0.83	0.91	0.86	0.82
2.50	1.00	0.88	0.97	0.92	0.87	0.82	0.81	0.77	0.80	0.76	0.74	1.00	0.88	0.97	0.92	0.87
3.00	1.05	0.92	1.02	0.96	0.90	0.86	0.85	0.82	0.83	0.81	0.78	1.05	0.92	1.02	0.96	0.90
4.00	1.11	0.96	1.07	1.01	0.95	0.91	0.90	0.87	0.88	0.86	0.83	1.11	0.96	1.07	1.01	0.95
5.00	1.14	0.98	1.11	1.04	0.97	0.94	0.93	0.90	0.91	0.89	0.86	1.14	0.98	1.11	1.04	0.97

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	17318	17318	17318	17318	17318	17318	17318
50.0	16992	16992	16992	16992	16992	16992	16992
55.0	16584	16584	16584	16584	16584	16584	16584
60.0	16128	16128	16128	16128	16128	16128	16128
65.0	15348	15348	15348	15348	15348	15348	15348
70.0	14392	14392	14392	14392	14392	14392	14392
75.0	13074	13074	13074	13074	13074	13074	13074
80.0	11307	11307	11307	11307	11307	11307	11307
85.0	8724	8724	8724	8724	8724	8724	8724
90.0	8753	8753	8753	8753	8753	8753	8753

(cd/m²)

2022-04-23