


Downlight 1 x 9290026750 6500K


1 x 600 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00


CIE flux code 46 78 95 100 100

UGRcen (4Hx8H, 0.25H) 29

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.47	0.45	0.47	0.46	0.45	0.37	0.37	0.32	0.36	0.32	0.30	0.30
0.80	0.58	0.55	0.57	0.56	0.54	0.46	0.46	0.41	0.45	0.40	0.38	0.38
1.00	0.67	0.62	0.66	0.64	0.62	0.54	0.53	0.48	0.52	0.48	0.46	0.46
1.25	0.76	0.70	0.74	0.71	0.69	0.62	0.61	0.56	0.60	0.55	0.53	0.53
1.50	0.82	0.75	0.80	0.77	0.74	0.67	0.66	0.61	0.65	0.61	0.58	0.58
2.00	0.92	0.83	0.90	0.86	0.82	0.76	0.75	0.70	0.73	0.70	0.67	0.67
2.50	0.99	0.88	0.96	0.91	0.86	0.82	0.80	0.76	0.79	0.76	0.73	0.73
3.00	1.04	0.91	1.01	0.95	0.90	0.86	0.84	0.81	0.83	0.80	0.77	0.77
4.00	1.10	0.95	1.07	1.00	0.94	0.91	0.89	0.86	0.87	0.85	0.82	0.82
5.00	1.14	0.98	1.10	1.03	0.97	0.94	0.92	0.90	0.90	0.88	0.85	0.85

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	33990	33990	33990	33990	33990	33990	33990
50.0	33439	33439	33439	33439	33439	33439	33439
55.0	32754	32754	32754	32754	32754	32754	32754
60.0	31859	31859	31859	31859	31859	31859	31859
65.0	30659	30659	30659	30659	30659	30659	30659
70.0	29041	29041	29041	29041	29041	29041	29041
75.0	26789	26789	26789	26789	26789	26789	26789
80.0	23816	23816	23816	23816	23816	23816	23816
85.0	19930	19930	19930	19930	19930	19930	19930
90.0	38129	38129	38129	38129	38129	38129	38129

(cd/m²)

2022-04-23