




Downlight 1 x 9290026749 4000K

1 x 600 lm

Polar intensity diagram**Quantity estimation diagram****UGR diagram**

Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00

CIE flux code 46 78 95 100 100

UGRcen (4Hx8H, 0.25H) 29

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.47	0.45	0.47	0.46	0.45	0.37	0.37	0.32	0.36	0.32	0.30	0.30
0.80	0.58	0.55	0.57	0.56	0.54	0.46	0.46	0.41	0.45	0.40	0.38	0.38
1.00	0.67	0.62	0.66	0.64	0.62	0.54	0.53	0.48	0.52	0.48	0.46	0.46
1.25	0.76	0.70	0.74	0.71	0.69	0.62	0.61	0.56	0.60	0.55	0.53	0.53
1.50	0.82	0.75	0.80	0.77	0.74	0.67	0.66	0.61	0.65	0.61	0.58	0.58
2.00	0.92	0.83	0.90	0.86	0.82	0.76	0.75	0.70	0.73	0.70	0.67	0.67
2.50	0.99	0.88	0.96	0.91	0.86	0.82	0.80	0.76	0.79	0.76	0.73	0.73
3.00	1.04	0.91	1.01	0.95	0.90	0.86	0.84	0.81	0.83	0.80	0.77	0.77
4.00	1.10	0.95	1.07	1.00	0.94	0.91	0.89	0.86	0.87	0.85	0.82	0.82
5.00	1.14	0.98	1.10	1.03	0.97	0.94	0.92	0.90	0.90	0.88	0.85	0.85

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	33984	33984	33984	33984	33984	33984	33984
50.0	33482	33482	33482	33482	33482	33482	33482
55.0	32849	32849	32849	32849	32849	32849	32849
60.0	32015	32015	32015	32015	32015	32015	32015
65.0	30927	30927	30927	30927	30927	30927	30927
70.0	29418	29418	29418	29418	29418	29418	29418
75.0	27271	27271	27271	27271	27271	27271	27271
80.0	24232	24232	24232	24232	24232	24232	24232
85.0	19804	19804	19804	19804	19804	19804	19804
90.0	21026	21026	21026	21026	21026	21026	21026

(cd/m²)

2022-04-23