




Downlight 1 x 9290026729 6500K

1 x 950 lm

Polar intensity diagram**Quantity estimation diagram****UGR diagram**

Light output ratio 1.00
 Service upward 0.01
 Service downward 0.99

CIE flux code 47 78 95 99 100

UGRcen (4Hx8H, 0.25H) 28

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.80	0.80	0.70	0.70	0.70
0.60	0.48	0.46	0.47	0.46	0.45	0.38	0.37	0.32	0.37	0.32	0.30	0.48	0.46	0.47	0.46	0.45
0.80	0.59	0.55	0.58	0.56	0.54	0.47	0.46	0.41	0.45	0.41	0.39	0.59	0.55	0.58	0.56	0.54
1.00	0.68	0.63	0.66	0.64	0.62	0.54	0.54	0.48	0.53	0.48	0.46	0.68	0.63	0.66	0.64	0.62
1.25	0.76	0.70	0.74	0.71	0.69	0.62	0.61	0.56	0.60	0.55	0.53	0.76	0.70	0.74	0.71	0.69
1.50	0.83	0.75	0.81	0.77	0.74	0.67	0.66	0.62	0.65	0.61	0.58	0.83	0.75	0.81	0.77	0.74
2.00	0.93	0.83	0.90	0.86	0.81	0.76	0.75	0.70	0.73	0.70	0.67	0.93	0.83	0.90	0.86	0.81
2.50	0.99	0.88	0.96	0.91	0.86	0.82	0.80	0.76	0.78	0.75	0.73	0.99	0.88	0.96	0.91	0.86
3.00	1.04	0.91	1.01	0.95	0.90	0.86	0.84	0.81	0.82	0.79	0.77	1.04	0.91	1.01	0.95	0.90
4.00	1.10	0.95	1.06	1.00	0.94	0.90	0.89	0.86	0.87	0.85	0.82	1.10	0.95	1.06	1.00	0.94
5.00	1.14	0.98	1.10	1.03	0.96	0.94	0.92	0.89	0.90	0.88	0.85	1.14	0.98	1.10	1.03	0.96

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	26967	26967	26967	26967	26967	26967	26967
50.0	26558	26558	26558	26558	26558	26558	26558
55.0	25977	25977	25977	25977	25977	25977	25977
60.0	25174	25174	25174	25174	25174	25174	25174
65.0	24185	24185	24185	24185	24185	24185	24185
70.0	22840	22840	22840	22840	22840	22840	22840
75.0	21262	21262	21262	21262	21262	21262	21262
80.0	19181	19181	19181	19181	19181	19181	19181
85.0	15779	15779	15779	15779	15779	15779	15779
90.0	26234	26234	26234	26234	26234	26234	26234

(cd/m²)

2022-04-04