




Downlight 1 x 9290026752 4000K

1 x 950 lm

Polar intensity diagram**Quantity estimation diagram****UGR diagram**

Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00

CIE flux code 46 78 95 100 100

UGRcen (4Hx8H, 0.25H) 28

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.47	0.45	0.47	0.46	0.45	0.37	0.37	0.32	0.36	0.32	0.30	0.30
0.80	0.58	0.55	0.57	0.56	0.54	0.46	0.46	0.41	0.45	0.40	0.38	0.38
1.00	0.67	0.62	0.66	0.64	0.62	0.54	0.53	0.48	0.52	0.48	0.46	0.46
1.25	0.76	0.70	0.74	0.71	0.69	0.62	0.61	0.56	0.60	0.55	0.53	0.53
1.50	0.82	0.75	0.80	0.77	0.74	0.67	0.66	0.61	0.65	0.61	0.58	0.58
2.00	0.92	0.83	0.90	0.86	0.82	0.76	0.75	0.70	0.73	0.70	0.67	0.67
2.50	0.99	0.88	0.96	0.91	0.86	0.82	0.80	0.76	0.79	0.76	0.73	0.73
3.00	1.04	0.91	1.01	0.95	0.90	0.86	0.84	0.81	0.83	0.80	0.77	0.77
4.00	1.10	0.95	1.07	1.00	0.94	0.91	0.89	0.86	0.87	0.85	0.82	0.82
5.00	1.14	0.98	1.10	1.03	0.97	0.94	0.92	0.90	0.90	0.88	0.85	0.85

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	27288	27288	27288	27288	27288	27288	27288
50.0	26865	26865	26865	26865	26865	26865	26865
55.0	26308	26308	26308	26308	26308	26308	26308
60.0	25592	25592	25592	25592	25592	25592	25592
65.0	24614	24614	24614	24614	24614	24614	24614
70.0	23236	23236	23236	23236	23236	23236	23236
75.0	21306	21306	21306	21306	21306	21306	21306
80.0	18623	18623	18623	18623	18623	18623	18623
85.0	14950	14950	14950	14950	14950	14950	14950
90.0	25376	25376	25376	25376	25376	25376	25376

(cd/m²)

2022-04-23