


DOWNLIGHT 1 x 9290026763 3000K


1 x 1500 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.01
 Service downward 0.99


CIE flux code 47 78 95 99 100

UGRcen (4Hx8H, 0.25H) 27

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.80	0.80	0.50	0.50	0.50	0.30	0.30	0.10	0.10	0.10	0.00	0.00
0.80	0.50	0.50	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
1.00	0.68	0.63	0.66	0.64	0.62	0.54	0.54	0.48	0.53	0.48	0.46	0.46
1.25	0.76	0.70	0.74	0.71	0.69	0.62	0.61	0.56	0.60	0.55	0.53	0.53
1.50	0.83	0.75	0.81	0.77	0.74	0.67	0.66	0.62	0.65	0.61	0.58	0.58
2.00	0.93	0.83	0.90	0.86	0.81	0.76	0.75	0.70	0.73	0.70	0.67	0.67
2.50	0.99	0.88	0.96	0.91	0.86	0.82	0.80	0.76	0.78	0.75	0.73	0.73
3.00	1.04	0.91	1.01	0.95	0.90	0.86	0.84	0.81	0.82	0.79	0.77	0.77
4.00	1.10	0.95	1.06	1.00	0.94	0.90	0.89	0.86	0.87	0.85	0.82	0.82
5.00	1.14	0.98	1.10	1.03	0.96	0.94	0.92	0.89	0.90	0.88	0.85	0.85

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	21360	21360	21360	21360	21360	21360	21360
50.0	20999	20999	20999	20999	20999	20999	20999
55.0	20548	20548	20548	20548	20548	20548	20548
60.0	19853	19853	19853	19853	19853	19853	19853
65.0	19154	19154	19154	19154	19154	19154	19154
70.0	18048	18048	18048	18048	18048	18048	18048
75.0	16469	16469	16469	16469	16469	16469	16469
80.0	14899	14899	14899	14899	14899	14899	14899
85.0	12437	12437	12437	12437	12437	12437	12437
90.0	24838	24838	24838	24838	24838	24838	24838

(cd/m²)

2022-04-04