




DOWNLIGHT 1 x 9290026758 4000K

1 x 950 lm



Light output ratio	1.00
Service upward	0.01
Service downward	0.99

CIE flux code 47 78 95 99 100

UGRcen (4Hx8H, 0.25H)	28
-----------------------	----

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80 0.80			0.70 0.70			0.50 0.50			0.30 0.30		
	0.80	0.50	0.30	0.70	0.50	0.30	0.70	0.50	0.30	0.70	0.50	0.30
0.60	0.48	0.46	0.47	0.46	0.45	0.38	0.37	0.32	0.37	0.32	0.30	
0.80	0.59	0.55	0.58	0.56	0.54	0.47	0.46	0.41	0.45	0.41	0.39	
1.00	0.68	0.63	0.66	0.64	0.62	0.54	0.54	0.48	0.53	0.48	0.46	
1.25	0.76	0.70	0.74	0.71	0.69	0.62	0.61	0.56	0.60	0.55	0.53	
1.50	0.83	0.75	0.81	0.77	0.74	0.67	0.66	0.62	0.65	0.61	0.58	
2.00	0.93	0.83	0.90	0.86	0.81	0.76	0.75	0.70	0.73	0.70	0.67	
2.50	0.99	0.88	0.96	0.91	0.86	0.82	0.80	0.76	0.78	0.75	0.73	
3.00	1.04	0.91	1.01	0.95	0.90	0.86	0.84	0.81	0.82	0.79	0.77	
4.00	1.10	0.95	1.06	1.00	0.94	0.90	0.89	0.86	0.87	0.85	0.82	
5.00	1.14	0.98	1.10	1.03	0.96	0.94	0.92	0.89	0.90	0.88	0.85	

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	26899	26899	26899	26899	26899	26899	26899
50.0	26445	26445	26445	26445	26445	26445	26445
55.0	25907	25907	25907	25907	25907	25907	25907
60.0	25047	25047	25047	25047	25047	25047	25047
65.0	24130	24130	24130	24130	24130	24130	24130
70.0	22812	22812	22812	22812	22812	22812	22812
75.0	21548	21548	21548	21548	21548	21548	21548
80.0	19240	19240	19240	19240	19240	19240	19240
85.0	16142	16142	16142	16142	16142	16142	16142
90.0	28623	28623	28623	28623	28623	28623	28623

(cd/m²)

2022-04-04