



RS060B G2 LDNR LED5-36 WH 1 x 9290026622 4000K**1 x 550 lm****Polar intensity diagram**

Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00


CIE flux code 90 99 99 100 100

UGRcen (4Hx8H, 0.25H) 22

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80 0.80		0.70 0.70		0.70 0.70		0.50 0.50		0.30 0.30		0.30 0.30		0.00 0.00		0.00 0.00	
	0.80	0.80	0.50	0.50	0.50	0.50	0.30	0.30	0.30	0.30	0.10	0.10	0.10	0.10	0.00	0.00
0.60	0.78	0.74	0.77	0.75	0.74	0.69	0.69	0.66	0.69	0.66	0.69	0.66	0.65			
0.80	0.86	0.80	0.85	0.82	0.80	0.76	0.75	0.72	0.75	0.72	0.75	0.72	0.71			
1.00	0.92	0.86	0.91	0.88	0.85	0.81	0.81	0.78	0.80	0.78	0.80	0.78	0.76			
1.25	0.98	0.90	0.97	0.93	0.89	0.86	0.85	0.83	0.84	0.82	0.84	0.82	0.81			
1.50	1.03	0.93	1.01	0.96	0.92	0.89	0.88	0.86	0.87	0.86	0.87	0.86	0.84			
2.00	1.09	0.98	1.07	1.02	0.97	0.95	0.93	0.92	0.92	0.91	0.92	0.91	0.89			
2.50	1.14	1.01	1.11	1.05	1.00	0.98	0.96	0.95	0.95	0.94	0.95	0.94	0.92			
3.00	1.17	1.02	1.14	1.07	1.02	1.00	0.99	0.97	0.97	0.96	0.97	0.96	0.94			
4.00	1.20	1.04	1.17	1.10	1.03	1.02	1.01	1.00	0.99	0.98	0.99	0.98	0.96			
5.00	1.23	1.05	1.19	1.11	1.04	1.03	1.02	1.01	1.00	1.00	1.00	1.00	0.97			

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	45670	45670	45670	45670	45670	45670	45670
50.0	11340	11340	11340	11340	11340	11340	11340
55.0	4728	4728	4728	4728	4728	4728	4728
60.0	3965	3965	3965	3965	3965	3965	3965
65.0	3814	3814	3814	3814	3814	3814	3814
70.0	4778	4778	4778	4778	4778	4778	4778
75.0	6032	6032	6032	6032	6032	6032	6032
80.0	5956	5956	5956	5956	5956	5956	5956
85.0	6753	6753	6753	6753	6753	6753	6753
90.0	0	0	0	0	0	0	0

(cd/m²)

2021-06-23