




RS061B G2 LDNR LED5-36 WH 1 x 9290026623 2700K**1 x 500 lm****Polar intensity diagram****Quantity estimation diagram****UGR diagram**

Light output ratio 1.00
Service upward 0.00
Service downward 1.00

CIE flux code 89 99 100 100 100

UGRcen (4Hx8H, 0.25H) 21

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80 0.80		0.70 0.70		0.70 0.70		0.50 0.50		0.30 0.30		0.30 0.30		0.00 0.00		0.00 0.00	
	0.50 0.50	0.30 0.10	0.50 0.50	0.30 0.10	0.50 0.50	0.30 0.10	0.30 0.10	0.10 0.10	0.30 0.10	0.10 0.10	0.30 0.10	0.10 0.10	0.10 0.10	0.10 0.10	0.10 0.10	0.00 0.00
0.60	0.77	0.73	0.76	0.75	0.73	0.69	0.68	0.66	0.68	0.65	0.64					
0.80	0.85	0.80	0.84	0.82	0.79	0.75	0.75	0.72	0.74	0.72	0.70					
1.00	0.92	0.85	0.91	0.88	0.85	0.81	0.80	0.78	0.80	0.77	0.76					
1.25	0.98	0.90	0.96	0.93	0.89	0.86	0.85	0.82	0.84	0.82	0.80					
1.50	1.02	0.93	1.01	0.96	0.92	0.89	0.88	0.86	0.87	0.85	0.84					
2.00	1.09	0.98	1.07	1.02	0.97	0.95	0.93	0.92	0.92	0.91	0.89					
2.50	1.14	1.01	1.11	1.05	1.00	0.98	0.97	0.95	0.95	0.94	0.92					
3.00	1.17	1.03	1.14	1.08	1.02	1.00	0.99	0.98	0.98	0.97	0.95					
4.00	1.21	1.05	1.17	1.10	1.04	1.02	1.01	1.00	0.99	0.99	0.97					
5.00	1.23	1.06	1.19	1.12	1.05	1.04	1.02	1.01	1.01	1.00	0.98					

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	50254	50254	50254	50254	50254	50254	50254
50.0	12805	12805	12805	12805	12805	12805	12805
55.0	5199	5199	5199	5199	5199	5199	5199
60.0	3479	3479	3479	3479	3479	3479	3479
65.0	3234	3234	3234	3234	3234	3234	3234
70.0	3827	3827	3827	3827	3827	3827	3827
75.0	4783	4783	4783	4783	4783	4783	4783
80.0	4593	4593	4593	4593	4593	4593	4593
85.0	4136	4136	4136	4136	4136	4136	4136
90.0	0	0	0	0	0	0	0

(cd/m²)

2021-06-23