



RS061B G2 LDNR LED5-36 PSR 1 x 9290026700 3000K**1 x 500 lm****Polar intensity diagram**

Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00


CIE flux code 88 99 100 100 100

UGRcen (4Hx8H, 0.25H) 21

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80				0.70				0.50			
	0.80	0.80	0.50	0.50	0.70	0.70	0.50	0.50	0.30	0.30	0.10	0.00
0.60	0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.10	0.00
0.80	0.76	0.73	0.76	0.74	0.72	0.68	0.67	0.65	0.67	0.64	0.63	0.63
1.00	0.84	0.79	0.83	0.81	0.79	0.74	0.74	0.71	0.73	0.71	0.70	0.70
1.25	0.91	0.85	0.90	0.87	0.84	0.80	0.80	0.77	0.79	0.77	0.75	0.75
1.50	0.98	0.89	0.96	0.92	0.89	0.85	0.84	0.82	0.84	0.81	0.80	0.80
2.00	1.02	0.93	1.00	0.96	0.92	0.89	0.88	0.86	0.87	0.85	0.83	0.83
2.50	1.09	0.97	1.07	1.01	0.97	0.94	0.93	0.91	0.92	0.90	0.89	0.89
3.00	1.14	1.00	1.11	1.05	1.00	0.98	0.96	0.95	0.95	0.94	0.92	0.92
4.00	1.17	1.02	1.14	1.07	1.02	1.00	0.99	0.97	0.97	0.96	0.94	0.94
5.00	1.21	1.04	1.17	1.10	1.03	1.02	1.01	1.00	0.99	0.99	0.96	0.96
5.00	1.23	1.05	1.19	1.11	1.04	1.04	1.02	1.01	1.00	1.00	0.97	0.97

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	45664	45664	45664	45664	45664	45664	45664
50.0	14675	14675	14675	14675	14675	14675	14675
55.0	5198	5198	5198	5198	5198	5198	5198
60.0	3107	3107	3107	3107	3107	3107	3107
65.0	2982	2982	2982	2982	2982	2982	2982
70.0	3394	3394	3394	3394	3394	3394	3394
75.0	3876	3876	3876	3876	3876	3876	3876
80.0	3832	3832	3832	3832	3832	3832	3832
85.0	3082	3082	3082	3082	3082	3082	3082
90.0	0	0	0	0	0	0	0

(cd/m²)

2021-06-23