

# PHILIPS

Creek Wall Light  
60W E27 No-bulb

myGarden

No bulb

Black

Water Resistant



15388/30/16



## Always light when you come home

Create a charming focal point for your entrance with this black Philips myGarden wall light. It's made from high-quality aluminium. With the motion sensor a welcoming pool of light ensures you walk safely into your home.

### Feel welcomed home with light

- Welcoming and reassuring light
- Easy-to-set-up sensor

### Design your garden with light

- Decorative outdoor lighting
- Choose heritage style
- Choose outdoor wall lights
- High-quality aluminium and superior synthetics

### Light up your garden with high-quality light

- Energy saving
- Powerful light

### Experience outdoor lighting easily

- Weather-proof

# Highlights

## Welcoming and reassuring light

The motion sensor switches on automatically when you come home and informs you when someone arrives.

## Easy-to-set-up sensor



A simple set-up procedure makes it easy to select when and for how long the automatic sensor switches on the lamp(s).

## Decorative outdoor lighting

Outdoor lighting can improve the look of your garden or outside space, illuminating eye-catching features, lighting pathways with style or creating the perfect ambience for those memorable evenings with friends and family. That's why Philips has created myGarden, a range of beautiful decorative outdoor lighting with the flair and functionality to help you make the most of your outdoor space in your own style.

## Choose heritage style

Designed in Europe, this lamp has a unique design signature to help you create a heritage outdoor look.

## Choose outdoor wall lights

Make the most of your outdoor space with this wall light, perfect for mounting close to your front door or on your terrace walls.

## High quality material

This Philips lamp is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high-quality die-cast aluminium and superior synthetics.

## Energy saving



This Philips light conserves energy compared to traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

## Powerful light

This outdoor lamp provides powerful warm white light. A bright pool of light to light up your garden or patio.

## Weather-proof



This Philips outdoor lamp is specially designed for humid outdoor environments and has undergone rigorous tests to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This lamp is designed with IP44: it is protected against splashing water. This product is most common and ideal for general outdoor use.

# Specifications

## Design and finishing

- Colour: Black
- Material: Aluminium

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

**Extra feature/accessory incl.**

- Fully weatherproof: Yes
- Motion sensor: Yes

**Garden area**

- Garden area: Garden and Patio

**Miscellaneous**

- Especially designed for: Garden and Patio
- Style: Classic
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Water Resistant

**Product dimensions and weight**

- Net weight: 0.717 kg
- Height: 28.5 cm
- Length: 17.5 cm
- Width: 20 cm

**Service**

- Warranty: 2 year(s)

**Technical specifications**

- Mains power: 50-60 Hz
- LED: No
- Energy class included light source: bulb not included
- Fitting/cap: E27
- Wattage bulb included: -
- Maximum wattage replacement bulb: 60 W
- IP code: IP44
- Class of protection: Class I
- Light source replaceable: Yes
- Number of light sources: 1

**Packaging dimensions and weight**

- EAN/UPC - product: 8718291443605
- Net weight: 0.72 kg
- Gross weight: 0.94 kg
- Height: 25.9 cm
- Length: 18.3 cm
- Width: 21.8 cm
- Material number (12NC): 915002791102



Issue date: 2024-07-25  
Version: 0.469

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)