

# PHILIPS

Calgary Wall Light  
60W E27 No-bulb

myGarden

No bulb

Inox

Water Resistant

17475/47/PN



## Illuminate your entrance automatically

The cylindrical Philips Calgary wall light with polished stainless steel look adds a modern look to your wall. It illuminates and lightens up your entrance with diffused and warm light. A motion sensor is integrated, so it switches on automatically when someone comes close.

### **Bring design into your garden**

- Choose contemporary style
- Choose outdoor wall lights
- High-quality stainless steel

### **Match your exterior style**

- Designed for outdoor use – water resistant IP44

### **Special characteristics**

- Welcoming and reassuring light
- Easy to set up for every application

### **Design your garden with light**

- Decorative outdoor lighting

# Highlights

## Choose contemporary style

Designed in Europe, this lamp has a unique design signature to help you create a contemporary outdoor look.

## Choose outdoor wall lights

Make the most of your outdoor space with this wall light, perfect for mounting close to your front door or on your terrace walls.

## High quality material

This Philips lamp is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high-quality stainless steel.

## Designed for outdoor use

This Philips outdoor light is especially designed for humid outdoor environments. It was tested rigorously to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This outdoor light is designed with IP44: it is protected against splashing water. This product is most commonly used and ideal for general outdoor use.

## Welcoming and reassuring light

The motion sensor switches on automatically when you come home and informs you when someone arrives.

## Easy to set up

### Decorative outdoor lighting

Outdoor lighting can improve the look of your garden or outside space, illuminating eye-catching features, lighting pathways with style or creating the perfect ambience for those memorable evenings with friends and family. That's why Philips has created myGarden, a range of beautiful decorative outdoor lighting with the flair and functionality to help you make the most of your outdoor space in your own style.

# Specifications

## Design and finishing

- Colour: Stainless steel
- Material: Glass, Metal

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable: Yes
- Fully weatherproof: Yes
- LED integrated: No
- Motion sensor: Yes

## Garden area

- Garden area: Garden and Patio

## Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Water Resistant

## Product dimensions and weight

- Net weight: 1.111 kg
- Overall height: 190 mm
- Overall length: 140 mm
- Overall width: 110 mm

## Service

- Warranty: 2 year(s)

### Technical specifications

- Bulb technology: LED
- Mains power: 50 Hz, 230 V
- Energy class included light source: bulb not included
- Fitting/cap: E27
- Wattage bulb included: -
- IP code: IP44
- Class of protection: Class II – Double Insulated
- Light source replaceable: Yes
- Number of light sources: 1

### The bulb

- Software upgradable: No

### What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

### Packaging dimensions and weight

- EAN/UPC – product: 8718696176764
- Net weight: 1.04 kg
- Gross weight: 1.13 kg
- Height: 20 cm
- Length: 12.5 cm
- Width: 14.5 cm



Issue date: 2026-05-30  
Version: 0.444

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)