


PHILIPS

Cinnabar Ceiling
Light 17 W

Ceiling Lights

2700K

White



33362/31/16



Decorate your home with light

Philips myLiving Cinnabar is a round ceiling light in white that illuminates areas in your home with a welcoming pool of warm white LED light. The pleasant diffused light is further enhanced by a ring that adds a glowing halo effect.

Sustainable light solutions

- Energy saving
- High quality LED light
- Warm white light
- Philips offers a 5-year warranty on the LED module and driver

Designed for your living room and bedroom

- Perfect to relax and socialise
- Create a stylish and welcoming atmosphere

Highlights

Energy saving



This Philips energy-saving lamp conserves energy compared with traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

High quality LED light



The LED technology integrated into this Philips lamp is a unique solution developed by Philips. It turns on instantly, enables an optimal light output and brings out vivid colours in your home.

Warm white light



Light can have different colour temperatures, indicated in units called Kelvin (K). Lamps with a low Kelvin value produce a warm, more cosy light, while those with a higher Kelvin value produce a cool, more energising light. This Philips lamp offers warm white light for a cosy atmosphere.

5-year warranty on LED system



On top of the standard 2-year warranty for this lamp, Philips offers a 5-year warranty on the LED system, meaning the LED module and the driver in this lamp.

Perfect to relax and socialise

The living room is the heart of any home: a place where families gather to relax and guests socialise. Lighting for your living room and bedroom has to be flexible and easy to adjust to its different uses throughout the day. Careful placement of different light sources and playing with light layering helps create the feeling of space and gives the room a warm and welcoming feel.

Create a stylish atmosphere



This light is designed around the latest tastes, trends and lifestyles to blend effortlessly into your décor and define the localised ambience you have always desired.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Colour: White
- Material: Metal, Plastic

Durability

- Number of switch cycles: 15,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Warm-up time to 60% light: 2
- Luminous efficacy (rated) (nom.): 88 lm/W

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes

Other characteristics

- Lamp current: 142 mA

Product dimensions and weight

- Net weight: 0.42 kg
- Overall height: 79 mm
- Overall length: 320 mm
- Overall width: 320 mm

Service

- Warranty: 5 year(s)

Technical specifications

- Light source equivalent to traditional bulb of: 24
- Diameter: 320 mm
- Total lumen output fixture: 1500
- Bulb technology: LED
- Light colour: 2700
- Mains power: AC 220-240
- Fixture dimmable: No
- IP code: IP20
- Class of protection: Class I – Earthed

Packaging dimensions and weight

- EAN/UPC – product: 8718696122785
- Net weight: 0.43 kg
- Gross weight: 0.7 kg
- Height: 8.7 cm
- Length: 34.4 cm
- Width: 34.4 cm



Issue date: 2025-08-30
Version: 0.638

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com