

PHILIPS

Kosipo Ceiling/Wall
Spotlight 2x

Ceiling/Wall Spotlights

No bulb

Black



50592/30/PN



Living joyfully in the moment

This Philips my Living Contemporary is a range of spot lights with elegant silhouettes and high quality light that matches today's tastes, trends and lifestyles.

Special characteristics

- Adjustable spot head
- The perfect light beam for accent lighting

Designed for your home office

- For any room in your interior
- Natural and recognisable forms

Designed for your living room and bedroom

- High-quality materials

Lighting for your convenience and peace of mind

- ClickFix easy mounting

Highlights

Adjustable spot head



Direct the light where you want it most by simply adjusting, rotating or tilting the spot head of the lamp.

Perfect for accent lighting

The perfect light beam for accent lighting. This Philips spot light has the perfect light beam for accent lighting (GU10 bulb not included). With bundled light you can emphasise any detail or feature in your interior.

For any room in your interior

Fully functional and at the same time very elegant, this Philips spot light will bring a decorative touch to any room in your home.

Natural and recognisable forms

Soft transitions and curved lines define the timeless look of myLiving by Philips. Practical and elegant, myLiving spot lights are unobtrusive and blend perfectly into any contemporary interior.

High-quality materials

This lamp is sculpted from layered patterns of high-quality materials with superior finishing. This ensures a solid and long lasting product that will enhance your home for many years to come.

ClickFix easy mounting



Install your spot light easily and by yourself. Thanks to ClickFix, no extra pair of hands is needed. Simply mount the bracket to the ceiling, connect the wires, then click and fix the lamp in one go.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Colour: Black
- Material: Metal

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Yes
- click!FIX mounting: Yes
- LED integrated: No

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Hallway
- Style: Contemporary
- Type: Ceiling/Wall Spotlights
- EyeComfort: No

Product dimensions and weight

- Net weight: 0.800 kg
- Height: 9.2 cm
- Length: 24 cm
- Width: 11.8 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Total lumen output fixture: No bulb included
- Mains power: AC 220-240
- Energy class included light source: bulb not included
- Fitting/cap: GU10
- Wattage bulb included: 5.5W
- Maximum wattage replacement bulb: 5.5
- IP code: IP20

- Class of protection: Class I
- Light source replaceable: Yes
- Number of light sources: 2

Packaging dimensions and weight

- EAN/UPC – product: 8718696164907
- Net weight: 0.8 kg
- Gross weight: 1 kg
- Height: 11.7 cm
- Length: 11.5 cm
- Width: 33.4 cm



Issue date: 2025-06-13
Version: 0.711

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com