

PHILIPS

Halogen capsule
bulb

Halogen

20 W

G4

Warm white

Dimmable



8711500413925



Stunning sparkling light

Philips capsule lamps provide crisp, sparkling halogen light, bringing out the best in your luminaire. All Philips capsules are fully dimmable.

Natural sparkling light

- Dimmable
- Bright halogen light provides contrast for better focus

Highlights

Dimmable

You control the level of light you need. Dimmable with all dimmers, this Philips halogen bulb can be adjusted from a bright, sparkling light to a warm, cosy glow.

Bright light, rich contrast

With the bright light of these Philips halogen lamps, contrasts get richer, letters become sharper and visibility gets better. Bright light is more relaxing for your eyes, allowing for a better focus.

Specifications

Bulb characteristics

- Lamp shape: Non-directional capsule
- Socket: G4
- Technology: Halogen
- Dimmable: Yes

Lamp dimensions

- Diameter: 10 mm
- Height: 33 mm
- Width: 10 mm

Durability

- Average life (at 2.7 hrs/day): 2 year(s)
- Lumen maintenance factor: 0.8
- Number of switch cycles: 8,000
- Nominal lifetime: 2,000

Light characteristics

- Application: Special application, Accent light
- Colour rendering index (CRI): 100
- Colour temperature: 2800 K
- Light Colour Category: Warm White
- Nominal luminous flux: 255 lm
- Starting time: 0 s
- Warm-up time to 60% light: Instant full light

Other characteristics

- Lamp current: not applicable mA

Power consumption

- Power factor: 1
- Voltage: 12 V
- Wattage equivalent: not applicable W
- Power: 20 W
- Energy consumption kWh/1,000 hours: 21.2

Rated values

- Rated lifetime: 2,000
- Rated luminous flux: 255 lm
- Rated peak intensity: not applicable cd
- Rated power: 20 W

Packaging dimensions and weight

- EAN/UPC - product: 8711500413925
- Net weight: 0 kg
- Gross weight: 0.01 kg
- Height: 12 cm
- Length: 0.8 cm
- Width: 14 cm



Issue date: 2025-12-24
Version: 0.637

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com