

PHILIPS

Shan Ceiling Light 12 W

Ceiling Lights

4000K

White

Sensor



8718699680558



Motion sensing light for convenience and extra energy saving

Increase convenience while saving energy. Philips' motion sensing LED ceiling light is easily turned on and off by a sensor which means you can leave or enter rooms without fumbling for a switch. Its wide detection range and instant-on LED technology means your home's lighting is only ever on when you need it.

Easy to experience

- With its built-in automatic motion sensor, this luminaire switches on automatically when people walk by.
- Easy installation

Premium quality

- EyeComfort – light that's easy on the eyes

Durability

- Energy saving
- Long life span up to 15,000 hours

Highlights

Integrated motion sensor

Easy installation

No more hassle with installation. Just fix or hang securely on the wall or ceiling, and plug it in. Your new light fitting is now ready to light up your room!

EyeComfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output and colour for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Energy saving

Saves energy – which is good for your bills, and the environment.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Colour: White
- Material: Metal, Plastic

Durability

- Number of switch cycles: 15,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Warm-up time to 60% light: 2
- Luminous efficacy (rated) (nom.): 104

Miscellaneous

- Especially designed for: Kitchen, Bedroom, Dining Room, Garage, Living Room, Office
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- Extra Features: Sensor

Other characteristics

- Lamp current: 108 mA

Product dimensions and weight

- Net weight: 0.38 kg
- Overall height: 80 mm
- Overall length: 260 mm
- Overall width: 260 mm

Service

- Warranty: 5 year(s)

Technical specifications

- Diameter: 260 mm
- Total lumen output fixture: 1250
- Bulb technology: LED
- Light colour: Cool white light
- Mains power: AC 220-240
- Fixture dimmable: No
- IP code: IP20 | Finger-protected
- Class of protection: Class I – Earthed

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8718699680558
- Net weight: 0.42 kg
- Gross weight: 0.54 kg
- Height: 8.2 cm
- Length: 30 cm
- Width: 30 cm



Issue date: 2026-04-15
Version: 0.418

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com