

PHILIPS

Reflector 60W R80
E27

LED

2700K

345 lm

15000 h



8718699773854



Durable LED accent lighting with a focused beam

This directional LED lamp provides a focused beam of warm, white light and is an excellent replacement for traditional reflector lamps.

High-quality light

- True incandescent-like warm white light

Highlights

True incandescent-like warm white light



This bulb has a colour temperature of 2,700 K, providing you with a warm, tranquil atmosphere, perfect for relaxing. This 2,700 K light is ideal for home lighting design.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E27
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Beam angle: 36
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 345 lm
- Warm-up time to 60% light: 0.4
- Colour Code: 827 | CCT of 2700K
- Luminous efficacy (rated) (nom.): 86

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

Packaging information

- EAN: 8718699773854
- EOC: 871869977385400
- Product title: LED CLA 60W R80 E27 WW 36D ND RF 1PF/4

Power consumption

- Power factor: 0.5
- Voltage: 220–240 V
- Wattage equivalent: 60
- Energy efficiency label (EEL): F
- Power: 4
- Energy consumption kWh/1,000 hours: 4

Product dimensions and weight

- Overall height: 112 mm
- Overall length: 112 mm
- Overall width: 80 mm

Rated values

- Rated peak intensity: 620 cd

Technical specifications

- Frequency: 50–60
- Bulb technology: LED
- EPREL Registration Number: 397592

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8718699773854
- Net weight: 0.14 kg
- Gross weight: 0.22 kg
- Height: 18.2 cm
- Length: 8.7 cm
- Width: 13 cm



Issue date: 2026-05-13
Version: 0.250

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com