

PHILIPS

Spot 35 W PAR16
GU10

LED

4000K

275 lm

15000 h



8718699774172



It's what's inside that makes the difference

With its beautifully shaped design and familiar dimensions, this LED spot is the perfect sustainable replacement for a traditional halogen spot.

High-quality light

- Cool, white light

Highlights

Cool, white light



This lamp has a colour temperature of 4000K providing you with an extra cool, fresh and crisp light.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Dimmable: No
- Lamp Finish: Clear
- Bulb material: Glass

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 36 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Nominal luminous flux: 275 lm
- Warm-up time to 60% light: 0.5
- Colour Code: 840 | CCT of 4000K
- Luminous efficacy (rated) (nom.): 78 lm/W

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

Packaging information

- EAN: 8718699774172
- EOC: 871869977417200
- Product title: LEDClassic 35W GU10 CW 36D RF ND SRT4

Power consumption

- Power factor: 0.5
- Voltage: 220–240 V
- Wattage equivalent: 35 W
- Energy efficiency label (EEL): F
- Power Consumption: 3.5 W
- Energy consumption kWh/1,000 hours: 4

Product dimensions and weight

- Overall height: 54 mm
- Overall length: 54 mm
- Overall width: 50 mm

Rated values

- Rated peak intensity: 590 cd

Technical specifications

- Frequency: 50–60
- EPREL Registration Number: 391857

Packaging dimensions and weight

- EAN/UPC – product: 8718699774172
- Net weight: 0.05 kg
- Gross weight: 0.07 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 6.3 cm



Issue date: 2025-11-12
Version: 0.160

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com