



## Bulb 60W A60 B22



Enjoy more convenience in everyday life with this smart WiZ LED A60 bulb. This bulb gives soft white light that dims to your desired brightness level via app or voice. You can set schedule to turn lights on and off according to your daily or weekly routines, and have remote access to your lights even when you're away. WiZ lights connect to your existing Wi-Fi, no additional hardware is needed.

## PRODUCT HIGHLIGHTS

- Dimmable warm white smart bulb
- Up to 806 lumens
- Easy plug and play
- Control with app or voice



### Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



### Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and get the lights to turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.



### Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.



### Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



### Illuminate with soft and warm white light

Create a cosy atmosphere with warm white light. A smart light that easily adapts to your daily activities.



### Dim your smart lights even without a dimmer

Simply adjust lights to your desired brightness level using your smartphone, the WiZ control accessory or just your voice. No need to install an expensive dimmer!



# SPECIFICATIONS

## BULB CHARACTERISTICS

Intended use: Indoor  
Lamp shape: A60  
Socket: B22  
Technology: Smart Wi-Fi  
Type of glass: Frosted  
Dimmable: Wireless Dim

## LAMP DIMENSIONS

Height: 12 cm  
Weight: 0.06 kg  
Width: 6 cm

## DURABILITY

Average life (at 2.7 hrs/day): 25 year(s)  
Lumen maintenance factor: 70%  
Number of switch cycles: 50,000  
Nominal lifetime: 25,000 h

## LIGHT CHARACTERISTICS

Colour consistency: 6 SDCM  
Colour rendering index (CRI): 90  
Colour temperature: 2700 K  
Light Colour Category: Warm White  
Nominal luminous flux: 806 lm  
Starting time: <0.5 s  
Warm-up time to 60% light: Instant full light

## OTHER CHARACTERISTICS

Lamp current: 70 mA  
Efficacy: 100 lm/W

## PACKAGING INFORMATION

EAN: 8718699786052  
EOC: 871869978605201  
Product title: Wi-Fi BLE 60W A60 B22  
927 DIM 1PF/6

## POWER CONSUMPTION

Power factor: 0.51  
Voltage: 220-240 V  
Wattage: 8 W  
Wattage equivalent: 60 W  
Energy efficiency label (EEL): F

## PRODUCT DIMENSIONS AND WEIGHT

Length: 12 cm

## RATED VALUES

Rated lifetime: 25,000 h  
Rated luminous flux: 806 lm  
Rated power: 8 W

## TECHNICAL SPECIFICATIONS

Frequency: 50-60 Hz  
EPREL Registration Number: 584555  
Flux measurement reference: Sphere



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.