



Wi-Fi BLE 75W G95 E27 927-65 TW 1PF/6



Think global and act local with these smart LED globe-shaped bulbs. So many uses around the house – vanity and bathroom lighting, playful pendants, special chandeliers and more. Choose from hundreds of shades of white light from cosy to cool, or schedule to automatically adjust to match your ever-changing needs and moods. All Wi-Fi controllable using the WiZ app, WiZ remote or your voice.

PRODUCT HIGHLIGHTS

- Tunable white smart bulb
- Up to 1055 lumens
- Easy plug and play
- Control with app or voice




Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and get the lights to turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.



Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Create your perfect light scene

Make your own mix of different colour and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energising cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: G95
Socket: E27
Technology: Smart Wi-Fi
Type of glass: Frosted
Dimmable: Wireless Dim

LAMP DIMENSIONS

Height: 13.9 cm
Weight: 0.13 kg
Width: 9.5 cm

DURABILITY

Average life (at 2.7 hrs/day): 25 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 25,000 h

LIGHT CHARACTERISTICS

Colour consistency: 6 SDCM
Colour rendering index (CRI): 90
Colour temperature: 2700-6500 K
Light Colour Category: Tunable white
Nominal luminous flux: 1055 lm
Starting time: <0.5 s
Warm-up time to 60% light: Instant full light

OTHER CHARACTERISTICS

Lamp current: 95 mA
Efficacy: 95 lm/W

PACKAGING INFORMATION

EAN: 8718699786335
EOC: 871869978633501
Product title: Wi-Fi BLE 75W G95 E27
927-65 TW 1PF/6

POWER CONSUMPTION

Power factor: 0.51
Voltage: 220-240 V
Wattage: 11 W
Wattage equivalent: 75 W
Energy efficiency label (EEL): F

PRODUCT DIMENSIONS AND WEIGHT

Length: 13.9 cm

RATED VALUES

Rated lifetime: 25,000 h
Rated luminous flux: 1055 lm
Rated power: 11 W

TECHNICAL SPECIFICATIONS

Frequency: 50-60 Hz
EPREL Registration Number: 584557
Flux measurement reference: Sphere



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.