



## Spot 50 W PAR16 GU10



Want a splash of colour? Have something special to display? Need to get something done? These full-colour LED spots can handle it all. Don't let the standard GU10 shape fool you: there's nothing standard about the light that comes out of these little powerhouses. Choose from millions of colours, or create schedules to automatically transition to the perfect ambiance as your needs and moods change. All Wi-Fi controllable using the WiZ app, WiZ remote or even your voice.

## PRODUCT HIGHLIGHTS

- Full colour smart bulb
- Up to 345 lumens
- Easy plug and play
- Control with app or voice



**Smart lighting functionalities easy to set up**  
Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!




**Exclusive SpaceSense™ light that turns on with movement**  
WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and get the lights to turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.



**Monitor your energy consumption**  
Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.



**Set up lights to follow your own schedule**  
Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



**Create your perfect light scene**  
Make your own mix of different colour and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



**Millions of colours and changing light modes to make your day**  
Choose any light colour you like or simply apply a dynamic light mode that we've designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



# SPECIFICATIONS

## BULB CHARACTERISTICS

Intended use: Indoor  
Lamp shape: PAR16  
Socket: GU10  
Technology: Smart Wi-Fi  
Type of glass: Frosted  
Dimmable: Wireless Dim

## LAMP DIMENSIONS

Height: 5.8 cm  
Weight: 0.05 kg  
Width: 5 cm

## DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)  
Lumen maintenance factor: 70%  
Number of switch cycles: 50,000  
Nominal lifetime: 15,000 h

## LIGHT CHARACTERISTICS

Beam angle: 36 degree(s)  
Colour consistency: 6 SDCM  
Colour rendering index (CRI): 90  
Colour temperature: 2200-6500 K  
Light Colour Category: Full colour  
Nominal luminous flux: 345 lm  
Starting time: <0.5 s  
Warm-up time to 60% light: Instant full light

## OTHER CHARACTERISTICS

Lamp current: 40 mA  
Efficacy: 73 lm/W

## PACKAGING INFORMATION

EAN: 8718699787134  
EOC: 871869978713401  
Product title: Wi-Fi BLE 50W GU10  
922-65 RGB 1PF/6

## POWER CONSUMPTION

Power factor: 0.51  
Voltage: 220-240 V  
Wattage: 4.7 W  
Wattage equivalent: 50 W  
Energy efficiency label (EEL): G

## PRODUCT DIMENSIONS AND WEIGHT

Length: 5.8 cm

## RATED VALUES

Rated beam angle: 36 degree(s)  
Rated lifetime: 15,000 h  
Rated luminous flux: 345 lm  
Rated peak intensity: 550 cd  
Rated power: 4.7 W

## TECHNICAL SPECIFICATIONS

Frequency: 50-60 Hz  
EPREL Registration Number: 804322  
Flux measurement reference: Narrow Cone



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.