

PHILIPS

Super Slim Ceiling Light 22 W

Ceiling Lights

2700K

White

Dimmable



8719514327061



One fixture. Your switch. Three light settings.

Create the right mood by changing brightness. Philips' SceneSwitch LED ceiling light lets you enjoy three brightness settings that are perfect for every moment. No dimmer or additional installation is required – all you need is your existing switch.

Designed for your living room and bedroom

- Perfect to relax and socialise

Match your interior

- Super slim design

Easy to experience

- Perfect for placement on wall or ceiling, the luminaire gives you the freedom to customise your look to match your interiors.
- Easy installation

Light effect

- Uniform light distribution

Premium quality

- EyeComfort – light that's easy on the eyes

Highlights

Perfect to relax and socialise

The living room is the heart of any home: a place where families gather to relax and guests socialise. Lighting for your living room and bedroom has to be flexible and easy to adjust to its different uses throughout the day. Careful placement of different light sources and playing with light layering helps create the feeling of space and gives the room a warm and welcoming feel.

Super slim design

Slim design is ideal for low-ceiling rooms, sitting flush against the surface.

Adaptable mounting for wall or ceiling Easy installation

No more hassle with installation. Just fix or hang securely on the wall or ceiling, and plug it in. Your new light fitting is now ready to light up your room!

Uniform light distribution

Throw light across your rooms in an even and uniform manner.

EyeComfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output and colour for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Specifications

Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

Design and finishing

- Colour: White
- Material: Metal, Plastic

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 20,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Warm-up time to 60% light: 2
- Luminous efficacy (rated) (nom.): 90

Miscellaneous

- Especially designed for: Kitchen, Bedroom, Dining Room, Garage, Living Room, Office
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- Extra Features: Dimmable

Other characteristics

- Lamp current: 110 mA

Product dimensions and weight

- Net weight: 1.13 kg
- Overall height: 23 mm
- Overall length: 430 mm
- Overall width: 430 mm

Service

- Warranty: 5 year(s)

Technical specifications

- Diameter: 430 mm
- Total lumen output fixture: 2000
- Bulb technology: LED
- Light colour: Warm white light
- Mains power: AC 220-240
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated

Packaging dimensions and weight

- EAN/UPC – product: 8719514327061
- Net weight: 1.11 kg
- Gross weight: 1.3 kg
- Height: 43 cm
- Length: 2.8 cm
- Width: 42.5 cm



Issue date: 2026-03-21
Version: 0.383

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com