

Utrecht Pedestal/Pathway  
Light 20W E27 No-bulb

Outdoor luminaires

No bulb

Anthracite

Water Resistant

8719514417533



## Enjoy a lovely garden with light

This Philips Utrecht outdoor pedestal in anthracite has an elegant design made of stainless steel. It creates a diffused glow for your garden, and brings social areas to sparkling life with its high-quality light.

### **Ease of use**

- No bulb included

### **Bring design into your garden**

- Choose for outdoor pedestal lights

### **Premium quality**

- High-quality stainless steel and superior synthetics

### **Designed for outdoors**

- IP44 – weatherproof

# Highlights

## No bulb included

This luminaire comes without a bulb, which enables you to chose the light output which is best suited to the room and your personal taste. Chosing a Philips LED bulb will ensure a high quality and long-lasting light output.

## Choose for outdoor pedestal lights

Make the most of your outdoor space with this pedestal light, perfect to light your garden, the edge of your terrace or to accentuate driveways and paths.

## High-quality stainless steel and superior synthetics

This Philips light is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high-quality stainless steel and superior synthetics.

## IP44 – weatherproof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water – perfect for general outdoor use.

# Specifications

## Bulb characteristics

- Dimmable: No

## Design and finishing

- Colour: Anthracite
- Material: Stainless Steel

## Durability

- Nominal lifetime: 0

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- click!FIX mounting: Yes
- Day-and-night sensor: No
- Defined light beams: No
- Dimmable: No
- Dimmable with remote control: No
- FFP – Frustration-Free Pack: No
- Fully weatherproof: Yes
- LED integrated: No
- Motion and day-and-night sensor: No
- Motion sensor: No
- Perfectly suited for creating ambience: No
- Perfectly suited for orientation lighting: No
- Portable: No
- Power adapter included: No
- Protection sleeve included: No
- Remote control included: No
- Resistant high-quality material: Yes
- Rotates freely in any direction: No
- Solar Energy: No
- Tilttable head (up-down): No
- USB charging: No
- Warm White Light: No
- Centrepiece: No
- Centrepiece: No
- Plug type: No plug

## Garden area

- Garden area: Garden and Patio

## Light characteristics

- Colour rendering index (CRI): >60
- Colour temperature: 2700 K

## Miscellaneous

- Especially designed for: Garden and Patio
- Style: Contemporary
- Type: Pedestal/Pathway Lights
- EyeComfort: No
- Extra Features: Water Resistant

## Product dimensions and weight

- Net weight: 0.48 kg
- Overall height: 45 mm
- Overall length: 12 mm
- Overall width: 12 mm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Diameter: 121 mm
- Total lumen output fixture: 0
- Light colour: 2700
- Mains power: AC 220-240
- Fitting/cap: E27
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class I – Earthed
- Light source replaceable: Yes
- Number of light sources: 1

## Packaging dimensions and weight

- EAN/UPC – product: 8719514417533
- Net weight: 0.48 kg
- Gross weight: 0.62 kg
- Height: 46 cm
- Length: 13 cm
- Width: 13 cm



Issue date: 2026-02-04  
Version: 0.492

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)