

# PHILIPS

Ozziet Ceiling Light  
18 W

Ceiling Lights


2700K

Black

Dimmable



8719514431928



## One fixture. Two light zones. Three settings.

This slim, sleek black ceiling light is designed to compliment your style. The sharp clean round lines of the main light are accented with a subtle linear edge light. Both lights work together to create three unique 2,700 k cool white light settings for a beautiful even light effect. The lamp is available in three sizes, and therefore fits perfectly in any room of your house. It is completed with a handy memory feature that can recall your latest setting. The Ozziet ceiling light looks as good off as it does on.

### Designed for your living room and bedroom

- Perfect to relax and socialise

### Match your interior

- Super slim design

### Easy to experience

- Memorise your favourite mode for easy selection
- Easy installation

### Light effect

- Dual zone light

# Highlights

## Perfect to relax and socialise

The living room is the heart of any home: a place where families gather to relax and guests socialise. Lighting for your living room and bedroom has to be flexible and easy to adjust to its different uses throughout the day. Careful placement of different light sources and playing with light layering helps create the feeling of space and gives the room a warm and welcoming feel.

## Super slim design

Slim design is ideal for low-ceiling rooms, sitting flush against the surface.

## Memorise your favourite mode for easy selection

Whether you prefer a warm glow for cosy evenings or a bright white light for focus, the system memorises your favourites for easy selection.

## Easy installation

No more hassle with installation. Just fix or hang securely on the wall or ceiling, and plug it in. Your new light fitting is now ready to light up your room!

## Dual zone light

Changing the ambiance in your room has never been easier. Philips' SceneSwitch Dual zone LED ceiling light lets you set the mood with three unique settings. The combination of main and linear edge light give you options that are perfect for your get together, concentrating and cosy moments. No dimmer or installation required – all you need is your existing switch.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

## Design and finishing

- Colour: Black
- Material: Plastic

## Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 20,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Warm-up time to 60% light: <2

## Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- Extra Features: Dimmable

## Other characteristics

- Lamp current: 150 mA
- Efficacy: 100 lm/W

## Product dimensions and weight

- Net weight: 0.61 kg
- Height: 4.5 cm
- Length: 30 cm
- Width: 30 cm

## Service

- Warranty: 5 year(s)

#### Technical specifications

- Diameter: 300 mm
- Total lumen output fixture: 1800
- Light colour: 2700
- Mains power: AC 220-240
- IP code: IP20
- Class of protection: Class II

#### Packaging dimensions and weight

- EAN/UPC – product: 8719514431928
- Net weight: 0.62 kg
- Gross weight: 0.88 kg
- Height: 32.5 cm
- Length: 5.4 cm
- Width: 32.5 cm



Issue date: 2025-05-13  
Version: 0.266

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)