

PHILIPS

Bulb 18.5 W (Eq.150 W) A80 E27

Smart LED

Full colour

Plastic

Easy plug and play

Control with WiZ app or voice



8719514437319



Colourful light that matches your mood

Bring colourful light to any standard lamp or fixture in your home with the high-lumen Philips smart LED full-colour bulb. This bulb is WiZ connected. Use with your existing Wi-Fi to control with the WiZ app or your voice.

Easy setup

- Easy plug and play

Smart control

- Control from anywhere with your smartphone
- Go hands-free with voice control

Smart features

- Automate your light with schedules

Light modes

- Millions of colours and dynamic light modes
- Tunable warm to cool white and preset modes
- Customise Scenes with preset dynamic light modes
- Light up your home with extra brightness

Highlights

Easy plug and play



WiZ works with your existing Wi-Fi router, no additional gateway is needed. Simply plug in your new light, download the WiZ app and you're ready to go!

Control from anywhere



Control your WiZ lights wherever you are with your smartphone. No need to worry if you've left your lights on before leaving home. The WiZ app is available for iOS and Android.

Go hands-free with voice control



Control your lights with just the sound of your voice, by simply enabling integration with Google, Alexa or add to your Siri shortcuts.

Automate your light with schedules

Automate the lights to fit your daily or weekly routines. Schedule your light to turn on before you arrive home and keep it off when not needed.

Millions of colours and dynamic light modes



Choose from a palette of millions of light colours to create an amazing atmosphere in your home. Enjoy the subtle differences that our dynamic light effects give your environment.

Tunable warm to cool white and preset modes



Choose from a wide range of energising cool white to soft warm white, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.

Customised Scenes



Mix different colour and white light modes to create the perfect light ambience for your daily moment. Save it and call it out at anytime with app, remote or voice.

Extra brightness



Brighten up your home with this high lumen light bulb. With sufficient brightness to help you engage in your tasks, or for relaxing activities, this light also works very well in large spaces with high ceilings.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: A80
- Socket: E27
- Type of glass: Frosted
- Lamp Finish: Frosted
- Dimmable: Yes

Lamp dimensions

- Weight: 0.3 kg

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Extra feature/accessory incl.

- LED integrated: Yes
- Solar Energy: No
- Warm glow dimmable light: No

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): ≥ 90
- Colour temperature: 2200–6500 K
- Light Colour Category: Full colour
- Nominal luminous flux: 2452 lm
- Starting time: < 0.5 s
- Warm-up time to 60% light: Instant full light
- Luminous efficacy (rated) (nom.): 132

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 140 mA

Packaging information

- EAN: 8719514437319
- EOC: 871951443731900
- Product title: PHI WFB 150W A80 E27 922-65 RGB 1PF/6

Power consumption

- Power factor: 0.5
- Voltage: 220–240 V
- Wattage equivalent: 150 W
- Energy efficiency label (EEL): E
- Power: 18.5 W
- Energy consumption kWh/1,000 hours: 19

Product dimensions and weight

- Overall height: 163 mm
- Overall length: 163 mm
- Overall width: 83 mm

Rated values

- Rated lifetime: 15,000
- Rated luminous flux: 2452 lm
- Rated power: 18.5 W

Service

- Warranty: 2 year(s)

Technical specifications

- Frequency: 50–60
- Bulb technology: LED
- EPREL Registration Number: 1901103
- Flux measurement reference: Sphere

What's supported

- Compatible with Effects feature: Yes
- WiFi: 802.11b/g/n
- Defined support period: Minimum of 60 months after introduction date
- Max. number of accessories: 9999
- Communication protocol: Bluetooth, WiFi (2.4GHz)
- Compatibility with third-party systems: Alexa, Google Home, Homey, IFTTT, Matter, Samsung SmartThings, Siri Shortcuts

Packaging dimensions and weight

- EAN/UPC - product: 8719514437319
- Net weight: 0.22 kg
- Gross weight: 0.31 kg
- Height: 21.6 cm
- Length: 10.5 cm
- Width: 10.7 cm



Issue date: 2026-03-25
Version: 0.209

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com