

# PHILIPS

Meranti Ceiling/Wall  
Spotlight 4x

Ceiling/Wall Spotlights


No bulb

Black

ClickFix



8719514465435



## The accent on style

Include this practical Philips spotlight in your home. Choose your Philips GU10 LED bulb to go with your spot style and ensure a high-quality and long-lasting light.

### Special characteristics

- Adjustable spot head

### Superior design for an optimal light effect

- Long-lasting, high-quality materials

# Highlights

## Adjustable spot head



Direct the light where you want it most by simply adjusting, rotating or tilting the spot head of the lamp.

## High quality material

This spot light is made of long-lasting, high-quality materials with superior finishing. This ensures a solid and durable product that will enhance and light up your home for many years to come.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Colour: Black
- Material: Metal

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- click!FIX mounting: Yes
- LED integrated: Yes

## Miscellaneous

- Especially designed for: Kitchen, Bedroom, Dining Room, Living Room, Office, Hall
- Style: Contemporary
- Type: Ceiling/Wall Spotlights
- EyeComfort: No
- Extra Features: ClickFix

## Product dimensions and weight

- Net weight: 0.665 kg
- Overall height: 150 mm
- Overall length: 674 mm
- Overall width: 80 mm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Total lumen output fixture: -
- Bulb technology: LED
- Mains power: AC 220-240
- Fitting/cap: GU10
- Wattage bulb included: 35W
- Maximum wattage replacement bulb: 35
- IP code: IP20 | Finger-protected
- Class of protection: Class I – Earthed
- Number of light sources: 4

## The bulb

- Software upgradable: No

## What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

## Packaging dimensions and weight

- EAN/UPC - product: 8719514465435
- Net weight: 0.67 kg
- Gross weight: 0.83 kg
- Height: 72 cm
- Length: 12 cm
- Width: 14 cm



Issue date: 2026-05-13  
Version: 0.334

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)