

PHILIPS

Mimosa Pedestal/ Pathway Light 7W

Outdoor luminaires

2700K

Antracite

Water Resistant



8719514477292



Easily direct high-quality LED light wherever you want it

The Mimosa family includes wall and ground lights in a brand-new design that allows you to direct the light wherever you want. Mimosa lights are made from high-quality aluminium. Their efficient LED modules and reliable electronics ensure a long useful life. Available in warm or cool white light.

Ease of use

- Adjustable light direction
- Wide light coverage

Sustainable light solutions

- Long lifetime up to 25,000 hours

Advanced LED light

- 5-year warranty on LED system
- High-quality LED light

Premium quality

- High-quality aluminium and superior synthetics

Designed for outdoors

- IP44 – weatherproof

Highlights

Adjustable light direction

A unique rotatable panel lets you easily direct light wherever you need it. Create the perfect light for all your outdoor activities – whether you're having dinner with family and friends on your patio or relaxing with a good book in your back garden.

Wide light coverage

This light provides more brightness for all of your outdoor spaces.

Long lifetime up to 25,000 hours



Reliable high-quality LED light lasts up to 25,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while enjoying the perfect garden light every night.

5-year warranty on LED system



In addition to the standard 2-year warranty offered for this luminaire, Philips also offers a 5-year warranty on the LED system (the LED module and driver).

High-quality LED light



These LED lights use a unique technology developed by Philips. They turn on instantly and produce optimal light output that brings out the vivid colours in your garden.

High-quality aluminium and superior synthetics



This Philips light is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high quality die-cast aluminium and superior synthetics.

IP44 – weatherproof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water – perfect for general outdoor use.

Specifications

Design and finishing

- Colour: Anthracite
- Material: Metal

Durability

- Nominal lifetime: 25,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: No
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: No
- Solar Energy: No
- Centrepiece: No

Garden area

- Garden area: Garden and Patio

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Pedestal/Pathway Lights
- EyeComfort: No
- Extra Features: Water Resistant

Product dimensions and weight

- Net weight: 0.663 kg
- Overall height: 250 mm
- Overall length: 120 mm
- Overall width: 120 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Total lumen output fixture: 630
- Light colour: Warm white light
- Mains power: 220-240
- Energy class included light source: F
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class I – Earthed
- Light source replaceable: No

Packaging dimensions and weight

- EAN/UPC - product: 8719514477292
- Net weight: 0.66 kg
- Gross weight: 0.79 kg
- Height: 27 cm
- Length: 7 cm
- Width: 15 cm



Issue date: 2025-12-27
Version: 0.324

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com