



## IMAGEO 1x adjustable spotlight

Highlight your home's decor using the adjustable spot and colourful smart light of the WiZ Imageo smart build-on spotlight in white. Use with your existing Wi-Fi to control with the WiZ app or your voice.

## PRODUCT HIGHLIGHTS

- Full colour
- Plate Dimensions: Ø8 cm
- IP20/Metal/White



### Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



### Control with any Matter smart home platform

This product is Matter-certified, allowing easy control through Google Home, Amazon Alexa, Apple Home or any other Matter-based smart home platform of your choice.



### Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and get the lights to turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.



### Create your perfect light scene

Make your own mix of different colour and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



### Millions of colours and changing light modes to make your day

Choose any light colour you like or simply apply a dynamic light mode that we've designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



### Set the right ambience with tunable warm to cool white light

Choose from a wide range of energising cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



# SPECIFICATIONS

## BULB CHARACTERISTICS

Intended use: Indoor  
Lamp shape: Rectangle  
Dimmable: Yes

## DESIGN AND FINISHING

Colour: White  
Material: Metal

## DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)  
Lumen maintenance factor: 70%  
Number of switch cycles: 50,000  
Nominal lifetime: 15,000

## EXTRA FEATURE/ACCESSORY INCL.

Dimmable with remote control: Yes  
LED integrated: No  
LED lamp(s) included: Yes  
Remote control included: No

## LIGHT CHARACTERISTICS

Colour rendering index (CRI):  $\geq 90$   
Colour temperature: 2200-6500 K  
Warm-up time to 60% light: 2  
Luminous efficacy (rated) (nom.): 69 lm/W

## MISCELLANEOUS

Especially designed for: Living Room  
Dining Room

## POWER CONSUMPTION

Voltage: 220-240 V

## PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.278 kg  
Overall height: 123 mm  
Overall length: 80 mm  
Overall width: 105 mm

## SERVICE

Warranty: 2 year(s)

## TECHNICAL SPECIFICATIONS

Lumen output bulb included: 345  
Total lumen output fixture: 345  
Light colour: 2200-6500 (RGB)  
Energy class included light source: G  
Wattage bulb included: 4.9  
Maximum wattage replacement bulb: 5  
IP code: IP20 | Finger-protected  
Class of protection: Class I – Earthed  
Light source replaceable: Yes  
Number of light sources: 1

## WHAT'S SUPPORTED

Compatible with Effects feature: Yes  
WiFi: Wireless G  
Defined support period: Minimum of 60 months after introduction date  
Max. number of accessories: 9999  
Communication protocol: Bluetooth  
WiFi (2.4GHz)

## PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8719514551879  
Net weight: 0.28 kg  
Gross weight: 0.37 kg  
Height: 14.5 cm  
Length: 8.3 cm  
Width: 10.7 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.